

2x**4113⁰⁰⁰****wolcraft®****82,0 x 5,5 x 1,1 mm****HM
CT**

AEG:	EH: 82, 450, 700, 700 A, 822, 825 H: 500, 750
Black&Decker:	BD: 710/11/13/25/35E DN: 710/12/30 KW: 710/11/13/25/35E P: 71-02, 71-03
Bosch:	GHO 3-82 PHO: 2-82, 3-82, 15-82, 25-82, 35-82-C, 100, 150, 200, 300
Casals:	CE 82
Fein:	HS 2151
Felisatti:	TP 282
Festo:	HL 750
Haffner:	FH 224
Hitachi:	F 20, F 20 A, F 20 SA, FP 20 A, FU 20, P 20 V
Holz Her:	2321, 2223
Legna:	G 82, R 82
Mafell:	EHU 82, MHU 82, GH 82 S
Makita:	1001, 1100, 1125 B, 1900 B, 1923 B, 1923 H
Metabo:	HO 3360, 4382, 0882, 8302
Perles:	HHB 82 B
Peugeot:	82 RA, BR 82, BRA 3-82, RA 400, RAC, RA 1082 CA
Skil:	94 H, 96 H
Stayer:	980 B
Ryobi:	L 120 N, 1323



wolcraft GmbH
Wolffstraße 1
56746 Kempenich
Germany
info@wolcraft.com
www.wolcraft.com



Y04 014244113