

7010000

wolcraft®



**TYP
050**

2000x

**6
mm
1/4"**



wolcraft GmbH
Wolffstraße 1
56746 Kempenich
Germany
www.wolcraft.com



wolcraft:

für • for • pour • per

Arrow: Powershot 5650, -5700, -8000, ETC 50, ETN 50, T 50, T 55

Black & Decker: A5753

Bosch: HMT 57

Esco: -11, Compacta N 500, HHT 11, Rallye 500

Emhard: POP 2000, -3000

Kwb: HT057

Lux: HHT mini! 196251, 195055, 101272

Mekano: MEK 16, -20, Hyper 16

Novus: J-16, J-19 EADHG, J-031 G, J-032 G, J-105 EADGH

Rapid: R11, -14, -24, -34E, -44, -64, -132, -211, -311, ESN114, CSN140, MS840, ALU740, -940

Rocafix: MS 50 V, ES130, HS50, MS15, -35, - 500, MS Metal

Stanley/Bostitch: Pro 14, Hammerstacker, TR100, -200, -250, -500, TR100 M2, T58, ET58 E, TR150 HL

tacocraft HT 10



Raccogli e differenzia.
Verifica le disposizioni
del tuo Comune



7010000
W42

