

7026000



**TYP
053**
2000x

**6
mm
1/4"**


4 006885 702608


 Raccolta differenziata.
Verifica le disposizioni
del tuo Comune

wolcraft:

Stanley/Bositch:

Rocagrat:

Rocafix:

Rapid:

Piranha:

Novus:

Lux:

Kwb:

Esco:

Einhell:

Bosch:

Black & Decker:

Arrow:

JT 21, T 27

A5751, A5752, A5980

HT 8, HT 14, HMT 53, PTK 14 E, PTK 3,6 LI

TC-CT 3,6 LI, TC-EN 20 E

Compacta 530, Decora 530, Derby 530, Esco 10, -20, -30,

-40 -50, -90, HT 53051, HT 53052, HT 53053, HT 53055

PT 8, PT 10, -PT 14, HT053, MT 10, T8, T9, T14, T17, TT14

HT Mini! 196250, 195015, 195000, 195040, 195060,

195010, 195020, 195030, Decotacker

J-01A, J-01AS, J-01, J-02, J-08 ABH, J-09 ABH,

J-16 EADHG, J-17, J-18, J-19 EADHG, J-19 EAD,

J-17 DA, J-102 DA, J-105 EADHG, J-214, EA J-316 A,

J-08XX, J-09XX

X 70004, X 70005, X 70006, X 70101, X 70102

R53, -153, -253, -353, -453, -553, MS4.1, M10R

MS 05, MS 20, MS 30, MS 40, MS 100, MS110,

MS 500, ES230, HS21, MS10

Fix 102, Fix 103, Fix 106, ROC 11

Hobby 8, HD 14, Pro 8, ST 10, ST 14, Vario 14,

TR45, TR150L, HammerTacker

6999, tacocraft HT8, tacocraft 8, Universal-Tacker,

Profi-Multifix, 7005, tacocraft 10, tacocraft 7,

tacocraft 14, tacocraft P10, tacocraft P14+,

tacocraft M10, tacocraft M14+, tacocraft ET14+, 7090

für • for • pour • per



wolcraft GmbH

Wolffstraße 1

56746 Kempenich

Germany

www.wolcraft.com



7026000 W42



702608