


7031000



**TYP
053**
1400x

**8
mm
5/16"**


4 006885 703100



Recicla
PAP
Verifica le disposizioni
del tuo Comune

wolfcraft:

Stanley/Bosstich:

Rocagrat:

Rocafix:

Rapid:

Piranha:

Novus:

Metabo:

Lux:

Kwb:

Esco:

Bosch:

Black & Decker:

Arrow:

AEG:

Powerlac 18, Powerlac 19

T 27, JT 21

A5751, A5752, A5980

PTK 14 E, PTK 19 E, HT 8, HT 14, HMT 53, PTK 3,6L!

Compacta 530, Decora 530, DLT 530, Esco 10, -20, -30, -40,

-50, -90, -100, HT 53052, HT 53053, HT 53055, HT 53056

T8, T9, T14, T17, T18, TT195, HT053, TT14, MT 10,

MT 16 N, PT 8, PT 10, PT 14 N, PT 18 N

HT Mini 196250, Decotacker, 195020, 195030,

Kunststofftacker 195015, 195000, 195010, 195040

TAA 19, TAE 1819, TAE 1919, TAE 2019, TAM 2020

J-01 A J-08 ABH, J-09 ABH, J-16 EAD, J-19 EAD, J-17,

J-16 EADHG, J-19 EADHG, J-08 XX, J-09XX, J-145,

J-155 A, J-165 EAD, J-219 Accu, J-105 EADHG

X 70004, X 70005, X 70006, X 70101, X 70102

R53, -153, -253, -353, -453, -553, ESN 530, MS610

MS 05, -20, -30 V, -40 V, -500B, ES 230, HS 21, MS 10,

MS100/110

Fix 102, Fix 103, Fix 106, ROC11

tacobrat 7, tacobrat 14, tacobrat P10, tacobrat P14+,

tacobrat M10, tacobrat M14+, tacobrat ET14+

für • for • pour • per



wolfcraft GmbH

Wolffstraße 1

56746 Kempenich

Germany

www.wolfcraft.com

7031000 W42

