

7032000

wolfcraft®

TYP
053

3000x

8
mm
5/16"

4 006885 703209

für • for • pour • per

AEG:

Powerlac 18, Powerlac 19

Arrow:

T 27, JT 21

Black & Decker:

A5751, A5752, A5980

Bosch:

PTK 14 E, PTK 19 E, HT 8, HT 14, HMT 53, PTK 3,6L!

Esco:

Compacta 530, Decora 530, DLT 530, Esco 10, -20, -30

HT 53056

Kwb:

T8, T9, T14, T17, TT18, TT19S, HT053, TT14, MT 10,

MT 16 N, PT 8, PT 10, PT 14 N, PT 18 N

Lux:

HT Mini! 196250, 195050, Decotacker, 195020,

195030, Kunststofftacker 195015, 195000, 195010,

195040

Metabo:

TAA 19, TAE 1819, TAE 1919, TAE 2019, TAM 2020

J-01 A J-08 ABH, J-09 ABH, J-16 EAD, J-19 EAD, J-17,

J-16 EADHG, J-19 EADHG, J-08 XX, J-09XX, J-145,

J-155 A, J-165 EAD, J-219 Accu, J-105 EADHG

Piranha:

X 70004, X 70005, X 70006, X 70101, X 70102

R53, -153, -253, -353, -453, -553, ESN 530, MS610

Rocafix:

MS 05, -20, -30 V, -40 V, -500B, ES 230, HS 21, MS 10,

MS100/110

Rocagrat:

Fix 102, Fix 103, Fix 106, ROC11

Stanley/Bosstich:

Hobby 8, HD 14, Pro 8, ST 10, -14, Vario 14, TR45

wolfcraft:

tacocraft ET 20, 6999, tacocraft HT 8, tacocraft 8,

Universal-Tacker, Profi-Multifix, 7005, tacocraft 10,

tacocraft 7, tacocraft 14, tacocraft P10, tacocraft P14+,

tacocraft M10, tacocraft M14+, tacocraft ET14+



①

Raccogli le differenziali.
Verifica le disposizioni
del tuo Comunewolfcraft GmbH
Wolffstraße 1
56746 Kempenich
Germany
www.wolfcraft.com7032000
W42

703209