




7032100

wolcraft®



**TYP
053**

**5000x
8
mm
5/16"**



Piranha: X 70004, X 70005, X 70006, X 70101, X 70102
Rapid: R53, -153, -253, -353, -453, -553, ESN 530, MS610
Rocafix: MS 05, MS 10, MS 20, MS 30 V, MS 40 V, MS 500B, ES 230, HS 21, MS100/110
Rocagrat: Fix 102, Fix 103, Fix 106, ROC11
Stanley/Bosch: Hobby 8, HD 14, Pro 8, ST 10, ST 14, Vario 14, TR45
wolcraft: tacocraft ET 20, 6999, tacocraft HT 8, tacocraft 8, Universal-Tacker, Profi-Multifix, 7005, tacocraft 10, tacocraft 7, tacocraft 14, tacocraft P10, tacocraft P14+, tacocraft M10, tacocraft M14+, tacocraft ET14+

AEG: Powerac 18, -19
Arrow: T 27, JT 21
Black & Decker: A5751, A5752, A5980
Bosch: PTK 14 E, PTK19 E, HT 8, HT14, HMT 53, PTK 3,6L!
Esco: Compacta 530, Decora 530, DLT 530, Esco 10, -20, -30, -40, -50, -90, -100, HT 53052, HT 53053, HT 53055, HT 53056
Kwb: T8, T9, T14, T17, TT18, TT19, HT053, TT14, MT 10, MT 16 N, PT 8, PT 10, PT 14 N, PT 18 N
Lux: HT Mini 196250, 195050, Decotacker, 195020, 195030, Kunststoffsack 195015, 195000, 195010, 195040
Metabo: TAA 19, TAE 1819, TAE 1919, TAE 2019, TAM 2020
Novus: J-01 A, J-08 ABH, J-09 ABH, J-16 EAD, J-19 EAD, J-17, J-16 EADHG, J-19 EADHG, J-08 XX, J-09XX, J-145, J-155 A, J-165 EAD, J-219 Accu, J-105 EADHG

für • for • pour • per



W42 - 7032100



Raccolta differenziata.
Verifica le disposizioni
del tuo Comune



wolcraft GmbH
Wolffstraße 1
56746 Kempenich
Germany
www.wolcraft.com

