

7036000

wolfcraft®

TYP
053

1000x

10
mm
3/8"

4 006885 703605



①
Raccogli e differenzia
Verifica le disposizioni
del tuo Comune

AEG:

Black & Decker:

Bosch:

Esco:

Kwb:

Lux:

Metabo:

Novus:

Piranha:

Rapid:

Rocafix:

Rocagrat:

Stanley/Bosstich:

wolfcraft:

für • for • pour • per

Powertac 18, Powertac 19

A5752, A5980

HT 14, PTK 14 E, PTK 19 E, PTK 3,6 L!

AT 53001, Compacta 530, DLT 530, HT 53053, Escro 10,

-30, -40, -50, -90, -100, ET 53031, HT53055

T14, T17, TT18, TT19S, TT28, TT14, MT 10,

MT 20 N, MT 16 N, PT 10, PT 14 N, PT 18 N

HT 195030, 195015, 195010, 195040, Tackermatic,

195060

TAE 1819, TAE 1919, TAE 2019, TAM 2020

J-02 AL, J-16, J-16 EAD, J-17, J-18, J-16 EADHG,

J-19 EADHG, J-19 EAD, J-145, J-155, J-155 A,

J-219 Accu, J-105 EADHG, J-17 DA, J-102 A

X 70005, X 70006

R253, R353, R453, R553, ESN530, MS853,

Compacta, R53E, R953, ALU753

MS 40 V, MS 500B, ES230, HS21, MS10, MS20, MS30,

MS100/110

Fix 106

HD 14, ST 10, ST 14, Vario 14

tacocraft ET 20, tacocraft HT 8, tacocraft 8,

Universal-Tacker, Profi-Multifix, tacocraft 10,

tacocraft 7, tacocraft 14, tacocraft P 10,

tacocraft P 14+, tacocraft M 10, tacocraft M 14+,

tacocraft ET 14+, 7100, electronic-Tacker



wolfcraft GmbH

Wolffstraße 1

56746 Kempenich

Germany

www.wolfcraft.com

7036000
W42

4 006885 703605