

703700

wolfcraft®

TYP
053

3000x

10
mm
3/8"

4 006885 703704

für • for • pour • per

AEG:

Black & Decker:

Bosch:

Esco:

Kwb:

Lux:

Metabo:

Novus:

Piranha:

Rapid:

Rocafix:

Rocagraf:

Stanley/Bosstitch:

wolfcraft:

Powerlac 18, Powerlac 19
A5752, A5980
HT 14, PTK 14 E, PTK 19 E, PTK 3,6 Li
AT 53001, Compacta 530, DLT 530, HT 53053, Esco 10
-30, -40, -50, -90, -100, ET 53031, HT53055
T14, T17, TT18, TT19S, TT28, TT14, MT 10,
MT 20 N, MT 16 N, PT 10, PT 14 N, PT 18 N
HT 195030, 195015, 195010, 195040,
Tackermatic, 195060
TAE 1819, TAE 1919, TAE 2019, TAM 2020
J-02 AL, J-16, J-16 EAD, J-17, J-18, J-16 EADHG,
J-19 EADHG, J-19 EAD, J-145, J-155, J-155 A,
J-219 Accu, J-105 EADHG, J-17 DA, J-102 A
X 70005, X 70006
R253, R353, R453, R553, ESN530, MS853,
Compacta, R53E, R953, ALU753
MS 40 V, MS 500B, ES230, HS21, MS10, MS20, MS30,
MS100/110
Fix 106
HD 14, ST 10, ST 14, Vario 14
tacocraft ET 20, tacocraft HT 8, tacocraft 8,
Universal-Tacker, Profi-Multifix, tacocraft 10,
tacocraft 7, tacocraft 14, tacocraft P 10,
tacocraft P 14+, tacocraft M 10, tacocraft M 14+,
tacocraft ET 14+, 7100, electronic-Tacker



Raccogli le disposizioni
Verifica le disposizioni
del tuo Comune



wolfcraft GmbH
Wolffstraße 1
56746 Kempenich
Germany
www.wolfcraft.com

703700
W42

4 006885 703704