



7037¹⁰⁰

wolcraft®



**TYP
053**

4000x



**10
mm**

3/8"

für • for • pour • per

AEG: Powertac 18, -19

Black & Decker: A5752, A5980

Bosch: HT 14, PTK 14 E, PTK 19 E, PTK 3,6 LI

Esco: AT 53001, Compacta 530, DLT 530, HT 53053, Esco 10, -30, -40, -50, -90, -100, ET 53031, HT53055

Kwb: T14, T17, TT18, TT195, TT28, TT14, MT 10, MT 20 N, MT 16 N, PT 10, PT 14 N, PT 18 N

Lux: HT 195030, 195015, 195010, 195040, Tackermatic, 195060

Metabo: TAE 1819, TAE 1919, TAE 2019, TAM 2020

Novus: J-02 AL, J-16, J-16 EAD, J-17, J-18, J-16 EADHG, J-19 EADHG, J-19 EAD, J-145, J-155, J-155 A, J-219 Accu, J-105 EADHG, J-17 DA, J-102 A

Piranha: X 70005, X 70006

Rapid: R253, R353, R453, R553, ESN530, MS853, Compacta, R53E, R953, ALU753

Rocafix: MS 40 V, MS500B, ES230, HS21, MS10, MS20, MS30, MS100/110

Rocagrat: Fix 106

Stanley/Bostitch: HD 14, ST 10, ST14, Vario 14

wolcraft: tacocraft ET 20, tacocraft HT 8, tacocraft 8, Universal-Tacker, Profi-Multifix, tacocraft 10, tacocraft 7, tacocraft 14, tacocraft P 10, tacocraft P 14+, tacocraft M 10, tacocraft M 14+, tacocraft ET 14+, 7100, electronic-Tacker



W42 - 7037¹⁰⁰



Raccolta differenziata.
Verifica le disposizioni
del tuo Comune



wolcraft GmbH
Wolffstraße 1
56746 Kempenich
Germany
www.wolcraft.com

