

7045000


wolcraft®

**TYP
053**
1000x

**14
mm
9/16"**

 Raccolta differenziata.
Verifica le disposizioni
del tuo Comune


AEG: Powerlac 18, -19
 Black & Decker: A5752
 Bosch: HT 14, PTK 14 E, -19 E, -23 E, -28 E
 Einhell: TC-CT 3,6 Li, TC-EN 20 E
 Escro: AT 53001, Compacta 530, DLT 530, Escro 30, -40, -50, -90, -100, ET 53031, HT 53053, HT 53055
 Kwb: T14, T17, TT18, TT19S, TT14, MT 14N, -16N, -20N
 Lux: 195015, 195010, 195040, 195030, Tackermatic
 Metabo: TAE 1819, TAE 1919, TAE 2019, TAM 2020
 Novus: J-16 EAD, J-19 EAD, J-17, J-18, J-16 EADHG, J-19 EADHG, J-102A, J-102 DA, J-105 EADHG, J-145, J-155, J-155 A, J-165 EAD, J-219 Accu, J-316 A, J-214 EA
 Piranha: X 70005, X 70006
 Rapid: R253, -353, -453, -553, ESN530, MS853, R953, ALU 753
 Rocafix: MS 500B, ES230
 Rocagrat: Fix 106
 Stanley/Bosch: Vario 14, HD 14, ST 14, TR150HL
 wolcraft: tacocraft ET 20, Universal-Tacker, Profi-Multifix, tacocraft 7, tacocraft 14, tacocraft P 14+, 7100, tacocraft M14+, tacocraft ET 14+, electronic-Tacker

für • for • pour • per



wolcraft GmbH

 Wolffstraße 1
56746 Kempenich

 Germany
www.wolcraft.com


7045000 W424

