

7046000



**TYP
053**
1000x

**14
mm
9/16"**


4 006885 704602



Raccogli e differenzia
Verifica le disposizioni
del tuo Comune

wolfcraft:

Stanley/Bosch: Vario 14, HD 14, ST 14, TR150HL

Rocagrat:

Fix 106

Rocafix:

MS 500B, ES230

Rapid:

ALU 753

Piranha:

R253, -353,-453, -553, ESN530, MS853, R953,

X 70005, X 70006

J-214 EA

Novus:

J-155, J-155 A, J-165 EAD, J- 219 Accu, J-316 A,

Metabo:

J-19 EADHG, J-102A, J-102 DA, J-105 EADHG, J-145,

Lux:

J-16 EAD, J-19 EAD, J-17, J-18, J-16 EADHG,

Kwb:

TAE 1819, TAE 1919, TAE 2019, TAM 2020

Escot:

195015, 195010, 195040, 195030, Tackermatic

Einhell:

T14, T17, T18, TT195, TT14, MT 14N, -16N, -20N

Bosch:

AT 53001, Compacta 530, DLT 530, Escot 30, -40,

Black & Decker:

-50, -90, -100, ET 53031, HT 53053, HT 53055

AEG:

TC-CT 3,6 Li, TC-EN 20 E

Bosch:

HT 14, PTK 14 E, -19 E, -23 E, -28 E

A5752

Powerac 18, -19

für • for • pour • per



wolfcraft GmbH

Wolffstraße 1

56746 Kempenich

Germany

www.wolfcraft.com



7046000 W42

4 006885 704602