

7047000

wolcraft®


**TYP
053**
3000x

**14
mm
9/16"**


107407 006885 4

für • for • pour • per

AEG:

Powerlac 18, -19

Black & Decker:

A5752

Bosch:

HT 14, PTK 14 E, -19 E, -23 E, -28 E

Einhell:

TC-CT 3,6 Li, TC-EN 20 E

Esco:

AT 53001, Compacta 530, DLT 530, Esco 30, -40, -50, -90, -100, ET 53031, HT 53053, HT 53055

Kwb:

T14, T17, TT18, TT19S, TT14, MT 14N, -16N, -20N

Lux:

195015, 195010, 195040, 195030, Tackermatic

Metabo:

TAE 1819, TAE 1919, TAE 2019, TAM 2020

Novus:

J-16 EAD, J-19 EAD, J-17, J-18, J-16 EADHG, J-19 EADHG, J-102A, J-102 DA, J-105 EADHG, J-145, J-155, J-155 A, J-165 EAD, J-219 Accu, J-316 A, J-214 EA

Piranha:

X 70005, X 70006

Rapid:

R253, -353,-453, -553, ESN530, MS853, R953, ALU 753

Rocafix:

MS 500B, ES230

Rocagrat:

Fix 106

Stanley/Bosstich:

Vario 14, HD 14, ST 14, TR150HL

wolcraft:

tacocraft ET 20, Universal-Tacker, Profi-Multifix, tacocraft 7, tacocraft 14, tacocraft P 14+, tacocraft M14+, tacocraft ET 14+, 7100, electronic-Tacker


 Raccolta differenziata.
Verifica le disposizioni
del tuo Comune

 wolcraft GmbH
Wolffstraße 1
56746 Kempenich
Germany
www.wolcraft.com


7047000 W42

4 006885 704701