



wolcraft GmbH
Wolffstraße 1
56746 Kempnich
Germany
info@wolcraft.com
www.wolcraft.com



max.
80 m/sec
13.300 rpm

EN
13236

X27 - 8381 000



8381 000

wolcraft®

STANDARD ★★☆☆

CERAMIC



Ø 110 mm

