

PE03055B



35 x 55

PE0406B




40 x 60

PE05075B



50 x 75

PE0608B




60 x 80

PE0710B



70 x 100

PE0812B




80 x 120

PE1015B




100 x 150

PE1217B




120 x 170

PE1622B




160 x 220

PE2030B




200 x 300

PE1825B




180 x 250

PE3020B



300 x 200

PE2515B



250 x 150

PE2212B



220 x 120

PE0415B




40 x 150

PE1020B




100 x 200

PE1030B




100 x 300

PE2020B




200 x 200

PE2525B



250 x 250

PE3030B



300 x 300

Data

Material :PE (Polyethylene)
 Thickness Specification :#05
 Actual Thickness :0.05mm (+0.05/-0.01)
 Color :Transparent
 Start heat melting temp. :110°C