

| Art.- No. | Bemessungswerte/Ratings/Valeurs assignées | | | Spannungsfall Voltage drop Chute de tension max [mV] | Verlustleistung Sustained dissip. Valeur de dissip. max [W] | Schmelzintegral Melting integral Intégral de fusion [A ² s] | |
|--------------|---|--------------------------------|--|---|--|---|---|
| | Strom Current Courant | Spannung Voltage Tension | Ausschaltvermögen Breaking capacity Pouvoir de coupure | | | | |
| 632.707 | 100 mA | 500 V | 1.000 A/ 500 V ~ | 2.500 | 1,6 | auf Anfrage/ on request/ à demande | |
| 632.708 | 125 mA | | | 2.000 | | | |
| 632.709 | 160 mA | | | 1.900 | | | |
| 632.710 | 200 mA | | | 1.500 | | | |
| 632.711 | 250 mA | | | 1.300 | 2,5 | | |
| 632.712 | 315 mA | | | 1.100 | | | |
| 632.713 | 400 mA | | | 1.000 | | | |
| 632.714 | 500 mA | | | 800 | | | |
| 632.715 | 630 mA | | | 700 | | | |
| 632.716 | 800 mA | | | 600 | | | |
| 632.717 | 1 A | | | 500 | | | |
| 632.718 | 1,25 A | | | 400 | | | |
| 632.719 | 1,6 A | | | 350 | | | |
| 632.720 | 2 A | | | 300 | | | |
| 632.721 | 2,5 A | | | 300 | | | 4 |
| 632.722 | 3,15 A | | | 250 | | | |
| 632.723 | 4 A | | | 200 | | | |
| 632.724 | 5 A | | | 150 | | | |
| 632.725 | 6,3 A | | | 150 | | | |
| 632.726 | 8 A | | | 150 | | | |
| 632.727 | 10 A | | | 150 | | | |

Aufbau: Keramikrohr, mit Löschmittel
 Kontaktkappen: Messing, vernickelt
 Verpackung: 100 St. = 10 x 10 Faltschachteln
 500 St. = Industrieverpackung

Construction: Ceramictube, with extinguishing agent
 Contact caps: Brass, nickel plated
 Packing: 100 pcs. = 10 boxes of 10 pieces
 500 pcs. = Industrial boxes

Construction: Tube céramique avec moyen d'extinction
 Cabochons de contact: Laiton, nickelé
 Emballage: 100 pcs. = en 10 boîtes de 10 pièces
 500 pcs. = en emballage industriel



Schmelzzeit-Grenzwerte / Pre-arcing time limits / Temps de fusion limité

| Bemessungsstrom Rated current Courant assigné | 2,1 I _{rat} | | 2,75 I _{rat} | | 4 I _{rat} | | 10 I _{rat} | |
|---|----------------------|--|-----------------------|------|--------------------|------|---------------------|--------|
| | max. | | min. | max. | min. | max. | min. | max. |
| 100 mA - 10 A | 900 s | | 400 ms | 20 s | 150 ms | 2 s | 20 ms | 300 ms |