



**DOUBLE DECK TERMINAL BLOCK
CENTRE MARKING WITH
HORIZONTAL JUMPERING ON
LOWER LEVEL**
281-620

| | |
|---|----------|
| ITEM-NO. (ITEM-NO.) | 281-630 |
| Cross section1 (Cross section / mm²) | 0.08 - 4 |
| Cross section2 (Cross section / AWG) | 28 - 12 |
| Strip length (Strip length / mm) | 9 - 10 |
| Measured voltage (Measured voltage / V) | 500 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 3 |
| Current intensity (Current intensity / A) | 26 |
| Height (Height / mm) | 58.5 |
| Width (Width / mm) | 6 |
| Depth (Depth / mm) | 83.5 |
| No. of connection Points (No. of connection Points) | 4 |
| No. of potentials (No. of potentials) | 2 |
| COLOR (COLOR) | blau |
| WEIGHT (WEIGHT / g) | 15.682 |