

**Mikrofonkabel**  
**Microphone Cable**

**Symmetrisches Patchkabel**  
**Balanced Patch Cable**

Studio  
Rack  
MIDI  
small diameter



Bestellnummer	Part No.	CPK 220 SW-BL-RT
<b>Mechanische Daten</b>	<b>Mechanical data</b>	
Leiterquerschnitt	Conductor area	0,20 mm <sup>2</sup>
Leiteraufbau	Composition of conductor	25 x 0,10 mm CU blank / bare copper
Leiterisolation	Conductor isolation	PE
Adernanordnung	Composition of cores	2 Adern zum Paar verseilt / 2 cores twinned
Paarschirm / Schirm	Pair screen / screen	Umseilung aus blanken Cu-Drähten / spiral wound copper wire screen
Gesamtmantel	Overall jacket	PVC, black-blue-red
Gesamtdurchmesser	Overall diameter	4,7 +/- 0,2 mm
Gewicht	Weight	31 g/m
Betriebstemperatur bewegt	Working temperature mobile	(-5°C) - (+70°C)
unbewegt	fixed	(-20°C) - (+70°C)
<b>Elektrische Daten</b>	<b>Electrical data</b>	
Leiterwiderstand	Conductor resistance	100 Ohm/km
Kapazität (Leiter / Leiter)	Capacity (cond./cond.)	90 pF/m
Kapazität (Leiter / Schirm)	Capacity (cond./screen)	160 pF/m
Prüfspannung	Test voltage	500 V eff.