

Mikrofonkabel
Microphone Cable

Symmetrisches Patchkabel
Balanced Patch Cable

Studio
Rack
MIDI
small diameter



| Bestellnummer | Part No. | CPK 220 SW-BL-RT |
|-----------------------------|----------------------------|--|
| Mechanische Daten | Mechanical data | |
| Leiterquerschnitt | Conductor area | 0,20 mm ² |
| Leiteraufbau | Composition of conductor | 25 x 0,10 mm CU blank / bare copper |
| Leiterisolation | Conductor isolation | PE |
| Adernanordnung | Composition of cores | 2 Adern zum Paar verseilt / 2 cores twinned |
| Paarschirm / Schirm | Pair screen / screen | Umseilung aus blanken Cu-Drähten / spiral wound copper wire screen |
| Gesamtmantel | Overall jacket | PVC, black-blue-red |
| Gesamtdurchmesser | Overall diameter | 4,7 +/- 0,2 mm |
| Gewicht | Weight | 31 g/m |
| Betriebstemperatur bewegt | Working temperature mobile | (-5°C) - (+70°C) |
| unbewegt | fixed | (-20°C) - (+70°C) |
| Elektrische Daten | Electrical data | |
| Leiterwiderstand | Conductor resistance | 100 Ohm/km |
| Kapazität (Leiter / Leiter) | Capacity (cond./cond.) | 90 pF/m |
| Kapazität (Leiter / Schirm) | Capacity (cond./screen) | 160 pF/m |
| Prüfspannung | Test voltage | 500 V eff. |