



## Bubblemat

Anti-Ermüdungsmatte mit genoppter Oberfläche aus einer schwer abnutzbaren Gummimischung. Die genoppte Oberfläche stimuliert konstant die Durchblutung und reduziert somit

Ermüdungserscheinungen in langen Stehphasen. Ideal für statische Steharbeitsplätze. Durch die Modulfunktion kann in der Breite von 0.60m jede beliebige Länge erreicht werden.

### Technische Angaben

Materialstärke: 14mm.

Schwarz

0,6m x 0,9m

0,9m x 1,2m

0,6m x 0,9m (Endmatte)

0,6m x 0,9m (Mittelmatte)



# Bubblemat



Product Height: 14mm

- Manufactured from a hard wearing rubber compound
- Comfortable standing surface – reduces fatigue
- Bubble surface stimulates blood circulation to feet
- Protects operators from cold concrete floors
- Ideal for use where operatives stand in static positions
- Standard mat (with safety bevelled edges) or middle and end sections for longer runs

Material:	Natural rubber								
Surface Finish:	Bubble shaped								
Product Height:	18 mm nominal								
Operating Temperature:	- 20° - + 160°								
Resistance to Chemicals:	Resistant to water and most mild acids								
Environmental Resistance:	Use predominantly in dry areas.								
UV Resistance:	N/A								
Typical Applications:	Ideal for manufacturing production areas where employees are standing in static positions. Bubble surface constantly stimulates blood circulation to reduce fatigue								
Installation Method:	Individual components that lock together to cover any desired length or individual mats complete with bevel edge all round								
Cleaning method:	Hose down or pressure wash using a mild detergent.								
<b>Product Performance:</b>	<table border="0"> <tr> <td>Fatigue:</td> <td>●●●●</td> </tr> <tr> <td>Slip Resistance:</td> <td>●●</td> </tr> <tr> <td>Wear:</td> <td>●●●●</td> </tr> <tr> <td>Low ‡ High</td> <td>●→●●●●</td> </tr> </table>	Fatigue:	●●●●	Slip Resistance:	●●	Wear:	●●●●	Low ‡ High	●→●●●●
Fatigue:	●●●●								
Slip Resistance:	●●								
Wear:	●●●●								
Low ‡ High	●→●●●●								
<b>Flame Retardancy:</b>	N/A								
<b>Country of Origin:</b>	INDONESIA								

Mat Size (m.) width x length	Weight Kg.	Packaging Size CM	Packaging Type	Packaging Quantity	Pallet Quantity	Colour	Part Code
0.6 x 0.9 (edged all round)	5	17.5 x 17.5 x 75	Boxed	1	42	Black	BF010001
0.9 x 1.2m (edged all round)	10	17.5 x 17.5 x 105	Boxed	1	30	Black	BF010002
0.6 x 0.9 (end piece)	5	17.5 x 17.5 x 75	Boxed	1	42	Black	BF010003
0.6 x 0.9 (middle)	5	17.5 x 17.5 x 75	Boxed	1	42	Black	BF010004

*The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that matting products may be subject to a degree of shrinkage when installed into some applications.*