



germanengineering

**BG 51 XXL
Glas-Diagnosewaage**

Besonders geeignet für schwergewichtige Personen:

- XXL-Waage mit riesiger Trittfläche aus extra starkem 8 mm Sicherheitsglas (39 x 30 cm)
- Tragkraft bis 200 kg

Körpergewicht, -fett, -wasser, Muskelanteil, Knochenmasse, Kalorienbedarf (AMR)

Mit BMI-Berechnung

Elektroden aus gebürstetem Edelstahl

Ziffernhöhe: 28 mm (Gewicht)

5 Aktivitätsgrade

200 kg Tragkraft

Einteilung:

- 0,1% für Körperfett, -wasser, Muskelanteil
- 100 g für Gewicht, Knochenmasse

Überlastungsanzeige

Umstellungsmöglichkeit von kg/lb/st

Quick-Start-Technologie

Abschaltautomatik

Produktabmessung: 39 x 30 x 2,5 cm

Inkl. 4 x 1,5V Batterie AAA

5 Jahre Garantie

Versandeinheit: 3 Transportkarton: -

EAN-Nr.: 42 11125 76020 5

Art.-Nr.: 760.20

**BG 51 XXL
Glass diagnostic scale**

Especially suited for heavy weight persons:

- XXL-scales with extra large platform of extra strong 8 mm safety glass (39 x 30 cm)
- 200 kg capacity

Body weight, body fat, body water, muscle ratio, bone mass, calory consumption (AMR)

With BMI calculation

Electrodes of brushed stainless steel

Digit size: 28 mm (Weight)

5 acitivity levels

200 kg capacity

Division:

- 0,1% body fat, body water, muscle ratio
- 100 g for body weight, bone mass

Overload indication

Change over to kg/lb/st

Quick-start technology

Automatic switch-off

Product measurements: 39 x 30 x 2.5 cm

4 x 1,5V battery AAA included

5 year guarantee

Sales unit: 3 Shipping carton: -

EAN no: 42 11125 76020 5

Item number: 760.20