

Audio/Video-Modulatoren

Audio/video modulators

Audio/Video-Modulator | stereo | VHF | UHF | S

Audio/video modulator | stereo | VHF | UHF | S

- ✓ Moduliert ein A/V-Signal in ein HF-Signal
- ✓ CCD-Überwachungskamera, Videokamera, DVD-Player etc. anschließbar
- ✓ VHF-/UHF-Kanal oder Sonderkanal wählbar
- ✓ LED-Display zur Kanalanzeige
- ✓ Inkl. Steckernetzteil, Cinch/SCART-Kabel, 2 x F/IEC-Kabel
- ✓ Modulates an AV signal into a RF signal
- ✓ CCD camera, video camera or DVD player etc. can be connected
- ✓ VHF/UHF channel or special channel between
- ✓ LED display for channel indication
- ✓ With plug-in power supply, cinch/SCART cable, 2 x F to IEC cable



Artikel Article	AVM 6-00
Artikelnummer Part No.	AVM00600
Verpackungseinheit Packing unit	1
CE	
Frequenzbereich Frequency range	47...862 MHz
VHF Kanäle VHF Channels	2...12
Sonderkanäle Special channels	S 2...40
UHF Kanäle UHF Channels	21...69
Übertragungsnorm Transmission norm	PAL B/G
Durchgangsdämpfung Through loss	4 dB
Ausgangspegel Output level	85 dB μ V
HF Ausgangsimpedanz RF Output impedance	75 Ohm
Video Eingangsimpedanz Video input impedance	75 Ohm
Audio Eingangsimpedanz Audio input impedance	10 kOhm
Video Eingangspegel Video input level	1 V _{SS}
Audio Eingangspegel Audio input level	1 V _{SS}
Anschlüsse HF RF Connectors	F-Buchse F-female
Anschlüsse Audio/Video Connectors audio/video	RCA/Cinch-Buchse RCA/cinch female
Steckernetzteil Power supply	230 V~/50 Hz 9 V= /300 mA
Maße (B x H x T) ca. Dimensions (W x H x D) appr.	120 x 90 x 30 mm

