

Audio/Video-Modulatoren

Audio/video modulators

TWIN Audio/Video-Modulator | mono | UHF

TWIN Audio/video modulator | mono | UHF

- ✓ Moduliert zwei A/V-Signale in zwei HF-Signale
- ✓ CCD-Überwachungskameras, Videokameras etc. anschließbar
- ✓ UHF-Kanal wählbar
- ✓ Aktive HF-Durchschleifung
- ✓ Ausgangspegel regelbar
- ✓ LED-Display zur Kanalanzeige
- ✓ Inkl. Steckernetzteil
- ✓ Modulates two AV signals into two RF signals
- ✓ CCD camera, video camera etc. can be connected
- ✓ UHF channel can be choosed
- ✓ Active RF-loop through
- ✓ Output level adjustable
- ✓ LED display for channel indication
- ✓ With plug-in power supply



Artikel Article	AVM 3-00
Artikelnummer Part No.	AVM00300
Verpackungseinheit Packing unit	1



Frequenzbereich Frequency range	470...862 MHz
Übertragungsnorm Transmission norm	PAL BG / PAL I / SECAM L
Durchgangverstärkung Through gain	2...4 dB
Ausgangspegel, einstellbar Output level, adjustable	70...90 dB μ V
HF Ausgangsimpedanz RF output impedance	75 Ohm
Video Eingangsimpedanz Video input impedance	75 Ohm
Audio Eingangsimpedanz Audio input impedance	10 kOhm
Video Eingangspegel Video input level	1 V _{SS}
Audio Eingangspegel Audio input level	1 V _{SS}
Anschlüsse HF RF connectors	F-Buchse F-female
Anschlüsse Audio/Video Connectors Audio/video	RCA/Cinch + SCART
Steckernetzteil Power supply	230 V - 50 Hz/3W 6V=1500 mA
Maße (B x H x T) ca. Dimensions (W x H x D) appr.	190 x 170 x 40 mm

