



MODEL	VOLTAGE		NO LOAD		AT MAXIMUM EFFICIENCY				STARTING		max. OUTPUT POWER W	POLES	CAPACITOR	BRUSHES
	Operating Range	Nominal	Speed	Current	Speed	Current	Torque	Output Power	Current	Torque				
	VDC	VDC	rpm	A	rpm	A	mNm	W	A	mNm				
SR540SA-4172P-67+C	10,0-13,0	12,0	9.900	0,47	8.392	2,59	23,55	20,90	14,41	154,61	40,48	3	2x47nF	carbon



Irrtum und Druckfehler vorbehalten / Errors and Omissions excepted