



MODEL	VOLTAGE		NO LOAD		AT MAXIMUM EFFICIENCY				STARTING		max. OUTPUT POWER W	POLES	CAPACITOR	BRUSHES
	Operating Range	Nominal	Speed	Current	Speed	Current	Torque	Output Power	Current	Torque				
	VDC	VDC	rpm	A	rpm	A	mNm	W	A	mNm				
SR545SA-4140P-67+C	10,0-13,0	12,0	9.752	0,57	8.132	2,84	26,42	21,83	14,24	159,08	39,40	5	2x47nF	carbon



Irrtum und Druckfehler vorbehalten / Errors and Omissions excepted