

Television Wall Bracket

00132032 WAB646 TV Wall Mount, VESA 200x200, tilt



Highlightstext:

- For the installation of flat screen TVs with a screen size from 25 to 117 cm (10" to 46")
- For all screens up to VESA 200x200
- Spirit level for accurate installation included
- Tilt design, tilt range: +15/-15°

Note for Consumers:

You additionally need the screw set 00118637 for televisions of the Sony W6/W7/W8xx series.

Technical characteristics:

- Drilling Template: No
- Hole Size Attachment: Up to M8
- Material: Steel Plate
- Maximum Load Capacity: 30 kg
- Model: TV
- Number of Joints: 0
- Rotation: 0 °
- Swivel Range: 0 °
- Tilt +/-: 15 / 15 °
- Vibration Damper: No
- Wall Distance min./max.: 6.85/6.85 cm
- Water Level: Yes
- External Dimension (Height): 22 cm
- External Dimension (Width): 25 cm
- Mounting Plate (Length): 25 cm
- Mounting Plate (Width): 10 cm
- Screen Dimensions: 102 cm (40"), 104 cm (41"), 107 cm (42"), 109 cm (43"), 112 cm (44"), 114 cm (45"), 117 cm (46"), 119 cm (47"), 125 cm (49"), 133 cm (53"), 136 cm (54"), 138.1 cm [55"], 143 cm (57"), 148 cm (59"), 151 cm (60"), 156 cm (62"), 158 cm (63"), 161 cm (64"), 166 cm (66"), 171 cm (68"), 174 cm (69"), 176 cm (70"), 180 cm (72"), 184 cm (74"), 186 cm (75"), 189 cm (76"), 191 cm (77"), 194 cm (78"), 197 cm (80"), 199 cm (81")
- Size: M
- VESA (from-to): 50x50 - 200x200
- VESA Standard: 100 x 100, 100 x 200, 200 x 100, 200 x 200, 50 x 50, 75 x 100, 75 x 75 mm
- Colour: Black
- Product Division: HiFi, TV & Home Cinema
- Shade of colour: Black
- Cable Manager: No
- Recommended Maximum Screen Size: 117 cm (46")
- Recommended Minimum Screen Size: 25 cm (10")
- Recommended Screen Size: 25 - 117 cm (10" – 46")
- Version: Tilting


Delivery:

- 1 WAB646 TV wall mount
- Mounting hardware
- 1 spirit level

Television Wall Bracket

00132032 WAB646 TV Wall Mount, VESA 200x200, tilt

- Mounting instructions

 4 047443 197955	Brand	Item-no.	VE	MB
	THOMSON	00132032	10	1