



sales@riotec.com.tw
 www.riotec.com.tw
 +886-2-8647-1828

Test Chart



High Density

Medium Density

Low Density

Code 39	 1234567890	 ABCDEFGH	 UV\$%+/-XYZ
Code 128	 CODE 128	 RIOTEC	 1234567890
CODABAR	 A0123456789A	 B9876543210B	 C12-\$/./+34C
Interleave 25	 1234567890	 1122334455	 6677889900
UPC	 0 432987 9	 1 23456 78901 2	 1 23456 78901 2
EAN/JAN	 1234 5670	 7 192751 043504 12345	 2 313541 343504

QR CODE



10mil 79 char



20mil 79 char



30mil 79 char

Datamatrix



11mil 60char



15mil 60char



20mil 382char

Aztec Code



12mil 79char



20mil 79char



40mil 79char

PDF 417



8mil 79char



10mil 79char



15mil 159char