



<b>Elevator 1xSchuko 1xUSB Doppelcharger</b>	<b>Elevator 1xSchuko 1xUSB Double Charger</b>
<b>Beschreibung:</b> <ul style="list-style-type: none"> <li>Versenk- und herausfahrbare Elektrifizierungseinheit für den Einbau in Küchenarbeitsplatten wie Holz, Schichtstoff, Naturstein oder Glas bzw. in Bürotische.</li> <li>Nach leichtem Druck auf den Deckel fährt die Einheit dank eines Federmechanismus aus und bietet eine komfortable und sichere Strom- und Datenzufuhr.</li> <li>Einfaches und flächenbündiges Versenken bei Nichtgebrauch.</li> <li>Befestigung mittels Schraubring.</li> </ul>	<b>Description:</b> <ul style="list-style-type: none"> <li>Ascending and descending electrification unit for installation for kitchen worktops like wood, laminated plastic, natural stone or glass resp. in office and conference tables.</li> <li>When pushing the lid the unit ascends due to a spring mechanism and offers a convenient and safe power and data supply.</li> <li>Simple and plain descending when not used.</li> <li>Mounting via ring nut.</li> </ul>
<b>Steckdosen:</b> <ul style="list-style-type: none"> <li>Nach IEC 60884, VDE 0620-1</li> <li>2-polig mit Schutzkontakt</li> <li>16A/3680W, AC250V, IP20, mit Kinderschutz</li> <li>Schwarz</li> </ul>	<b>Sockets:</b> <ul style="list-style-type: none"> <li>According IEC 60884, VDE 0620-1</li> <li>2-pole with earthing contact</li> <li>16A/3680W, AC250V, IP20, with child protection</li> <li>Black</li> </ul>
<b>Daten:</b> <ul style="list-style-type: none"> <li>1xUSB Doppelcharger 5.2V/2,15A mit 2xUSB Ports A</li> </ul>	<b>Data:</b> <ul style="list-style-type: none"> <li>1xUSB Double Charger 5.2V/2,15A with 2xUSB ports A</li> </ul>
<b>Anschluss:</b> <ul style="list-style-type: none"> <li>2,0m H05VV-F 3G1,5mm<sup>2</sup> schwarz mit beiliegendem Schutzkontaktstecker</li> </ul>	<b>Connection:</b> <ul style="list-style-type: none"> <li>2.0m H05VV-F 3G1,5mm<sup>2</sup> black with German type plug enclosed</li> </ul>
<b>Befestigung:</b> <ul style="list-style-type: none"> <li>In rundem Ausschnitt mit Ø80mm (+/-1mm)</li> <li>Für Plattenstärken von 16mm bis 60mm</li> <li>Fixierung über Schraubring</li> </ul>	<b>Mounting:</b> <ul style="list-style-type: none"> <li>In round hole with Ø80mm (+/-1mm)</li> <li>For mounting in plates with thicknesses from 16mm to 60mm</li> <li>Mounting via ring nut</li> </ul>
<b>Material:</b> <ul style="list-style-type: none"> <li>Kunststoff:Schwarz, PA6 GF 30 V1, Glühdraht-Prüfung bis 850°C</li> <li>Profil: Aluminium glänzend poliert, „Edelstahl-Look“, Strangguss</li> <li>Blenden: Edelstahl gestanzte und gebürstet</li> </ul>	<b>Material:</b> <ul style="list-style-type: none"> <li>Plastic: Black, PA6 GF 30 V1, glow wire resistant up to 850°C</li> <li>Profile: Aluminum polished "stainless steel look", continuous casting</li> <li>Aperture: Stainless steel brushed and stamped</li> </ul>
<b>Abmessungen in mm:</b> <ul style="list-style-type: none"> <li>Siehe Zeichnung</li> </ul>	<b>Measurements in mm:</b> <ul style="list-style-type: none"> <li>According to drawing</li> </ul>
<b>Lieferform:</b> <ul style="list-style-type: none"> <li>In Kartonbox verpackt</li> </ul>	<b>Packing:</b> <ul style="list-style-type: none"> <li>In carton box</li> </ul>
<b>Lieferumfang:</b> <ul style="list-style-type: none"> <li>1x Elevator</li> <li>1x Montageanleitung</li> </ul>	<b>Extent of delivery:</b> <ul style="list-style-type: none"> <li>1x Elevator</li> <li>1x Mounting instruction</li> </ul>