

## Conductive Copper foil Tape



Best. Nr.	Typ. (model)	Tape Dimension
1569011	CU-F2.5R1000	W: 25 mm x L: 10 meter
1569012	CU-F5.0R1000	W: 50 mm x L: 10 meter

### Specification

Structure	: Conductive Copper Foil
Backing adhesive	: Conductive Acrylic Adhesive
Foil thickness	: 0.018 mm
Total thickness	: 0.05 mm
Color	: Copper

### Technical Data

Adhesion Strength	: $\geq 4.5$ N/cm
Tensile strength	: $\geq 40$ / cm
Rating Voltage	: <600V
Breakdown strength	: <6kv
Temperature resistance	: 120°C max.