

# Datasheet

Item no. 1576723, 1576724, 1576725, 1576726, 1576727



**Aufbau:**  
Glasrohr, durchsichtig  
**Kontaktkappen:**  
Messing, vernickelt

**Construction:**  
Glasstube, transparent  
**Contact caps:**  
Brass, nickel plated

## Bemessungswerte / Ratings

Art.-No.	Strom Current (A)	Spannung Voltage	Ausschaltvermögen Breaking capacity	Spannungsfall Voltage drop (Volt) max.	Max. Verlustleistung Max. Power dissip. [W]	Schmelzintegral Melting integral [A <sup>2</sup> s]
TC-UL632.320	2 A	250 V	200 A	0,32	1,0	61
TC-UL632.360	3 A	250 V	200 A	0,22	1,1	146
TC-UL632.323	4 A	250 V	200 A	0,19	1,2	226
TC-UL632.324	5 A	250 V	200 A	0,16	1,3	349
TC-UL632.325	6 A	250 V	200 A	0,16	1,6	286

Electrical Characteristics

Prüfstrom Testing current	Schmelzzeit / Blow Time	
	Minimum	Maximum
100 %	4 Hrs	N / A
135 %	N / A	1 Hr
200 %	5 sec	30 sec