

Datasheet

Item no. TC-MK323

SPECIFICATIONS:

RATING: 125VAC 6A, 250VAC 3A
 CONTACT RESISTANCE: 20mΩ MAX.
 INSULATION RESISTANCE: 500VDC 100MΩ MIN.
 DIELECTRIC STRENGTH: 1500VAC 1 MINUTE
 OPERATING TEMPERATURE: -20°C <-> +65°C
 ELECTRICAL LIFE: 50,000 MAKE AND BREAK CYCLES AT FULL LOAD.



9	TERMINAL	BRASS 0.6T, SILVER PLATED	2
8	TERMINAL	BRASS 0.6T, SILVER PLATED	4
7	ENCLOSURE	PFS, BLUE/ BLACK COLOR	1
6	SHIELDED	STEEL,NICKEL PLATED	1
5	ZIGZAG WASHER	65Mn, NICKEL PLATE ON TEENTH	1
4	FIX WASHER	STEEL, NICKEL-PLATED	1
3	HEX NUT	BRASS NICKEL-PLATED	2
2	BODY	BRASS NICKEL-PLATED	1
1	HANDLE BAR	BRASS NICKEL-PLATED	1
NO.	PART NAME	MATERIAL	Q`TY

