

Datasheet

Item no. TC-MK245

Specification

1. Rating:3A 125VAC;1.5A 250VAC
2. Contact resistance:20mΩ max
3. Insulation resistance:500VDC 1000MΩ min
4. Dielectric strength:1000VAC,1Minute
5. Operating Temperature:-25°C~+85°C
6. Electrical Life:10,000 Cycles



Circuitry trait

| 02 | ON | - | ON |

