

HUAWEI SuperCharge Adapter

4.5V/5A(EU)+5A Type-C Data Cable

EN Input: 100-240V	Output: 5V $\overline{=}$ 2A / 4.5V $\overline{=}$ 5A / 5V $\overline{=}$ 4.5A	Length: 100cm
FR Entrée: 100-240V	Sortie: 5V $\overline{=}$ 2A / 4.5V $\overline{=}$ 5A / 5V $\overline{=}$ 4.5A	Longueur: 100cm
ES Entrada: 100-240V	Salida: 5V $\overline{=}$ 2A / 4.5V $\overline{=}$ 5A / 5V $\overline{=}$ 4.5A	Longitud: 100cm
RU Вход: 100-240В	Выход: 5В $\overline{=}$ 2А / 4.5В $\overline{=}$ 5А / 5В $\overline{=}$ 4.5А	Длина: 100см
DE Eingang: 100-240V	Ausgang: 5V $\overline{=}$ 2A / 4.5V $\overline{=}$ 5A / 5V $\overline{=}$ 4.5A	Länge: 100cm
IT Input: 100-240V	Output: 5V $\overline{=}$ 2A / 4.5V $\overline{=}$ 5A / 5V $\overline{=}$ 4.5A	Lunghezza: 100cm
NL Ingang: 100-240V	Uitgang: 5V $\overline{=}$ 2A / 4.5V $\overline{=}$ 5A / 5V $\overline{=}$ 4.5A	Langte: 100cm
PT Entrada: 100-240V	Saída: 5V $\overline{=}$ 2A / 4.5V $\overline{=}$ 5A / 5V $\overline{=}$ 4.5A	Comprimento: 100cm
AR الشاحن: 100-240 فولت	الخارج: 5 فولت $\overline{=}$ 2 أمبير / 4.5 فولت $\overline{=}$ 5 أمبير / 5 فولت $\overline{=}$ 4.5 أمبير	الطول: 100 سم

MODEL: AP81 (HW-050450E00)



All images on the packaging are for reference only, the actual product may differ from images on the packaging (including but not limited to colors, shape, and screen display).

Huawei Technologies Co., Ltd.
Huawei Industrial Base, Bantian,
Longgang, Shenzhen 518129,
People's Republic of China
Made In China

Huawei Tech Investment Co., Ltd.
C/O Huawei Technologies Netherlands B.V.
Herikerbergweg 36, 1101CM
Amsterdam, Netherlands
Website: consumer.huawei.com