



Made in Germany

AccuLux SL 7/SL 8 LED



Arbeitsleuchte mit Notlichtfunktion (geht an bei Stromausfall)
Work Lamp with emergency function



AccuLux SL 7 LED Set
Ohne Linsenfokus:
für breite
Lichtstreuung



AccuLux SL 8 LED Set
Mit Linsenfokus:
für hohe Leuchtweite



NEU! NEW!
3 Jahre Akku-Garantie!
3 years warranty for
battery!

AccuLux SL 7 LED



AccuLux SL 8 LED

AccuLux SL 7 LED Set (Art.Nr. 456641)
ohne Linsenfokus: breite Lichtstreuung

AccuLux SL 8 LED Set (Art.Nr. 456741)
mit Linsenfokus für hohe Leuchtweite

Handscheinwerfer mit modernster LED- und Akku-Technologie!
In Gebäuden oder Fahrzeugen montierbar. 3-stufig schaltbar:
Hauptlicht, Pilotlicht und Blinklicht.

Der **Lithium-Eisenphosphat-Akku** (LiFePO4) hat eine sehr geringe
Selbstentladung und ist mit ca. 2000 Ladezyklen 4 mal langlebiger
als herkömmliche Akkus! Dadurch wiegt die Leuchte nur noch
730 g (vorher: 1100 g).

Technische Daten:

- Hauptlicht: Power LED mit ca. 200 Lumen
- Pilotlicht: Nichia LED 5 mm
- Leuchtdauer: ca. 5 h (Hauptlicht); ca. 165 h (Pilotlicht)
- Schutzart: IP 54 (Leuchte)
- Akku: LiFePO4, 3,2 V / 3,4 Ah
- Ladezeit: ca. 5 h
- Leuchtweite: bis ca. 150 m
- Maße: 104 x 245 x 120 mm (Leuchte + Ladeeinheit)

Lieferumfang: Leuchte, Ladestation, Ladekabel 230 V und 12/24 V,
Streuscheibe orange

AccuLux SL 7 LED Set (Art.Nr. 456641)
no focused lens: widespread light

AccuLux SL 8 LED Set (Art.Nr. 456741)
incl. focused lens: for long range

Work lamp with hightech-technology of LED and rechargeable
battery! For installation in buildings and vehicles. 3-step switch:
Main light, emergency light and Flash-light.

The **Lithium-Iron Phosphate battery** (LiFePO4) has a very low
discharge factor: therefore the longevity is 4 times higher than of
common batteries (can be charged 2000 times instead of 500
times) **Result:** The weight of the lamp is 730 g only (before 1100 g).

Technical Data:

- Main lamp: Power LED ca. 200 Lumens
- Pilot lamp: Nichia LED 5 mm
- Light time: ca. 5 h (main lamp); ca. 165 h (Emergency light)
- Protect. class: IP 54 (Lamp)
- Battery: LiFePO4, 3,2 V / 3,4 Ah
- Charging time: ca. 5 h
- Range: ca. 150 m
- Dimension: 104 x 245 x 120 mm (Lamp + Charging unit)

Supply: Lamp, Charging unit, Charging cable 230 V and 12/24 V,
diffuser orange