

# H07V-K / (H)07V-K

PVC-Single Cores, fine wire stranded



## Technical data

- PVC single cores to  
DIN VDE 0285-525-2-31/  
DIN EN 50525-2-31 and IEC 60227-3
- **Temperature range**  
flexing -5°C to +70°C  
fixed installation -30°C to +80°C
- **Nominal voltage**  
U<sub>0</sub>/U 450/750 V
- **Test voltage**  
2500 V
- **Insulation resistance**  
min. 10 MOhm x km
- **Minimum bending radius**  
fixed installation  
core Ø ≤ 8 mm: 4x core Ø  
core Ø > 8-12 mm: 5x core Ø  
core Ø > 12 mm: 6x core Ø
- **Radiation resistance**  
up to 80x10<sup>6</sup> cJ/kg (up to 80 Mrad)

## Cable structure

- Bare Cu-conductor, to  
DIN VDE 0295 cl.5, fine wire,  
BS 6360 cl.5, IEC 60228 cl.5
- Core insulation of PVC  
compound type T11 to  
DIN VDE 0207-363-3 / DIN EN 50363-3  
and IEC 60227-3
- Core identification: see table below

## Properties

- The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers

## Tests

- PVC self-extinguishing and flame retardant acc. to DIN VDE 0482-332-1-2, DIN EN 60332-1-2, IEC 60332-1-2 (equivalent DIN VDE 0472 part 804 test method B)

## Note

- The following colours are recommended (only single colour): black, white, blue, grey, brown, red, orange, turquoise, violet and pink. Two-coloured combinations are not allowed, with exceptions of green-yellow.
- Colours yellow, green, transparent only in (H)07V-K available.
- Two-coloured combination is only permitted for (H)07V-K.

## Application

These single cores are suitable for laying in tubes, under and surface mounting of plasters and also in closed installation conduits. These are not allowed to install for direct laying on cable trays, channels or tanks. These types are permitted for the inner wiring of equipment, distributor and switchboards and also for protective laying to the lightings with a nominal voltage up to 1000 V alternating current or up to 750 V direct current against earth.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

## H07V-K, (H)07V-K

Cross-sec. mm <sup>2</sup> app. RAL	Outer Ø min. - max. mm	Cop. weight kg / km	BK	GN-YE	BU	BN	RD	WH	GY	VT	YE	PK	GN	TRANS	D-BU	OG	2-col.	U-BU
			9005	-	5015	8003	3000	9003	7001	4005	1021	3015	6018	-	5010	2003	-	5002



### Coil in cardboard (100m)

#### Packing

##### H07V-K coil

Part no.	Outer Ø min. - max. mm	Cop. weight kg / km	29129	29130	29131	29132	29133	29134	29135	29136	29137	29138	29139	29140	29141	29142	29144	26395
1,5	2,8 - 3,4	14,4																
2,5	3,4 - 4,1	24,0	29145	29146	29147	29148	29149	29150	29151	29152	29153	29154	29155	29156	29157	29158	29160	26396
4	3,9 - 4,8	38,0	29161	29162	29163	29164	29165	29166	29167	29168	29169	29170	29171	29172	29173	29174	29176	26397
6	4,4 - 5,3	58,0	29177	29178	29179	29180	29181	29182	29183	29184	29185	29186	29187	29188	29189	29190	29192	26398



### Spool (with various capacity)

#### Packing

##### H07V-K spool

Part no.	Outer Ø min. - max. mm	Cop. weight kg / km	26690	26691	26692	26693	26694	26695	26696	26697	26698	26699	26700	26701	26702	26703	26705	26399
1,5	2,8 - 3,4	14,4																
2,5	3,4 - 4,1	24,0	26706	26707	26708	26709	26710	26711	26712	26713	26714	26715	26716	26717	26718	26719	26721	26400
4	3,9 - 4,8	38,0	26722	26723	26724	26725	26726	26727	26728	26729	26730	26731	26732	26733	26734	26735	26737	26401
6	4,4 - 5,3	58,0	26738	26739	26740	26741	26742	26743	26744	26745	26746	26747	26748	26749	26750	26751	26753	26402

Continuation ►

# H07V-K / (H)07V-K

PVC-Single Cores, fine wire stranded

H05V-U, (H)05V-U, (H)07V-U



Cross-sec. mm <sup>2</sup>	Outer Ø min. - max. mm	Cop. weight kg / km	BK	GN-YE	BU	BN	RD	WH	GY	VT	YE	PK	GN	TRANS	D-BU	OG	2-col.	U-BU
app. RAL			9005	-	5015	8003	3000	9003	7001	4005	1021	3015	6018	-	5010	2003	-	5002



**Packing**

**Barrel (with various capacity)**

H07V-K barrel																			
Part no.			26755	26756	26757	26758	26759	26760	26761	26762	26763	26764	26765	26766	26767	26768	26770	26403	
1,5	2,8 - 3,4	14,4																	
Part no.			26771	26772	26773	26774	26775	26776	26777	26778	26779	26780	26781	26782	26783	26784	26786	26404	
2,5	3,4 - 4,1	24,0																	
Part no.			26787	26788	26789	26790	26791	26792	26793	26794	26795	26796	26797	26798	26799	26800	26802	26819	
4	3,9 - 4,8	38,0																	
Part no.			26803	26804	26805	26806	26807	26808	26809	26810	26811	26812	26813	26814	26815	26816	26818	26820	
6	4,4 - 5,3	58,0																	



**Packing**

**Coil in foil (100m)**

H07V-K coil																			
Part no.			26060	26061	26062	26063	26064	26065	26066	26067	26068	26069	26092	26099	26108	26109	26111	26821	
1,5	2,8 - 3,4	14,4																	
Part no.			26112	26113	26114	26115	26116	26117	26118	26119	29855	29856	29857	29858	29859	29890	29892	26822	
2,5	3,4 - 4,1	24,0																	
Part no.			29893	29894	29895	29896	29897	29898	29899	29905	29906	29907	29908	29909	29910	29911	29913	26823	
4	3,9 - 4,8	38,0																	
Part no.			29914	29915	29916	29917	29918	29919	29921	29922	29923	29924	29925	29926	29927	29928	29933	26824	
6	4,4 - 5,3	58,0																	
Part no.			29193	29194	29195	29196	29197	29198	29199	29200	29201	29202	29203	29204	29205	29206	29208	-	
10	5,7 - 6,8	96,0																	
Part no.			29209	29210	29211	29212	29213	29214	29215	29216	29217	29218	29219	29220	29221	29222	29224	-	
16	6,7 - 8,1	154,0																	
Part no.			29225	29226	29227	29228	29229	29230	29231	29232	29233	29234	29235	29236	29237	29238	29240	-	
25	8,4 - 10,2	240,0																	
Part no.			29241	29242	29243	29244	29245	29246	29247	29248	29249	29250	29251	29252	29253	29254	29256	-	
35	9,7 - 11,7	336,0																	
Part no.			29257	29258	29259	29260	29261	29262	29263	29264	29265	29266	29267	29268	29269	29270	29272	-	
50	11,5 - 13,9	480,0																	
Part no.			29273	29274	29275	29276	29277	29278	29279	29280	29281	29282	29283	29284	29285	29286	29288	-	
70	13,2 - 16,0	672,0																	
Part no.			29289	29290	29291	29292	29293	29294	29295	29296	29297	29298	29299	29300	29301	29302	29304	-	
95	15,1 - 18,2	912,0																	
Part no.			29418	29419	29420	29421	29422	29423	29424	29425	29426	29427	29428	29429	29430	29431	29433	-	
120	16,7 - 20,2	1152,0																	
Part no.			29434	29435	29436	29437	29438	29439	29440	29441	29442	29443	29444	29445	29446	29447	29449	-	
150	18,6 - 22,5	1440,0																	
Part no.			29494	29495	29496	29497	29498	29499	29590	29591	29592	29593	29594	29595	29596	29597	29599	-	
185	20,6 - 24,9	1776,0																	
Part no.			29813	29814	29815	29816	29817	29818	29819	29840	29841	29842	29843	29844	29845	29846	29848	-	
240	23,5 - 28,4	2304,0																	



**Packing**

**Drum**

H07V-K drum																			
Part no.			26825	26826	26827	26828	26829	26830	26831	26832	26833	26834	26835	26836	26837	26838	26840	-	
10	5,7 - 6,8	96,0																	
Part no.			26841	26842	26843	26844	26845	26846	26847	26848	26849	26850	26851	26852	26853	26854	26856	-	
16	6,7 - 8,1	154,0																	
Part no.			26857	26858	26859	26860	26861	26862	26863	26864	26865	26866	26867	26868	26869	26870	26872	-	
25	8,4 - 10,2	240,0																	
Part no.			26873	26874	26875	26876	26877	26878	26879	26880	26881	26882	26883	26884	26885	26886	26888	-	
35	9,7 - 11,7	336,0																	
Part no.			26889	26890	26891	26892	26893	26894	26895	26896	26897	26898	26899	26900	26901	26902	26904	-	
50	11,5 - 13,9	480,0																	
Part no.			26905	26906	26907	26908	26909	26910	26911	26912	26913	26914	26915	26916	26917	26918	26920	-	
70	13,2 - 16,0	672,0																	
Part no.			26921	26922	26923	26924	26925	26926	26927	26928	26929	26930	26931	26932	26933	26934	26936	-	
95	15,1 - 18,2	912,0																	
Part no.			29305	29306	29307	29308	29309	29310	29311	29312	29313	29314	29315	29316	29317	29318	29320	-	
120	16,7 - 20,2	1152,0																	
Part no.			29321	29322	29323	29324	29325	29326	29327	29328	29329	29330	29331	29332	29333	29334	29336	-	
150	18,6 - 22,5	1440,0																	
Part no.			29337	29338	29339	29340	29341	29342	29343	29344	29345	29346	29347	29348	29349	29350	29352	-	
185	20,6 - 24,9	1776,0																	
Part no.			29353	29354	29355	29356	29357	29358	29359	29360	29361	29362	29363	29364	29365	29366	29368	-	
240	23,5 - 28,4	2304,0																	
Part no.			28878	28879	28880	28881	28882	28883	28884	28885	28886	28887	28888	-	28889	28890	28891	-	
300	26,0 - 30,5	2880,0																	

Dimensions and specifications may be changed without prior notice. (RK01)