

DIN 7968

Sechskant-Passschrauben
für Stahlkonstruktion



Maße	M 12	M 16	M 20	M 26	M 27	M 30
b	20,5	24,5	28,5	33	35,5	38,5
k	8	10	13	15	17	19
$d_s \text{ min.}$	12,74	16,74	20,71	24,71	27,71	30,67
s	18	24	30	36	41	46

mit Mutter nach ISO 4032 oder ISO 4034