

LBT-120BK

Turntable with Bluetooth and USB Direct Encoding



EN

- Bluetooth transmission (2.1+EDR)
- Direct MP3 encoding, from vinyl to USB stick
- Integrated stereo pre-amplifier
- 2 rated speed settings 33 RPM and 45 RPM
- Moving Magnetic Cartridge (MMC)
- Mechanical arm lift
- Belt drive
- Semi-automatic
- Auto return
- Track splitting
- Removable plastic dust cover
- Connections: USB port

DE

- Bluetooth übertragung (2.1+EDR)
- MP3-Direktenkodierung, von Vinyl auf USB-Stick
- Integrierter Stereo-Vorverstärker
- 2 Geschwindigkeiten 33 U/min und 45 U/min
- Moving Magnetic Cartridge (MMC)
- Mechanischer Tonarmlift
- Riemenantrieb
- Halbautomatisch
- Automatische Rückführung des Tonarms
- Track-Splitting
- Abnehmbare Staubschutzhaube aus Kunststoff
- Anschlussbuchse : USB-Eingang

NL

- Bluetooth transmission (2.1+EDR)
- Directe MP3 codering van Vinyl naar USB-stick
- Ingebouwde stereo voorversterker
- 2 snelheden 33 RPM en 45 RPM
- Moving Magnetic Cartridge (MMC)
- Mechanische arm lift
- Riemaandrijving
- Semi-automatisch
- Auto return
- Track splitting
- Afneembare stofkap
- Aansluiting: USB aansluiting

FR

- Transmission Bluetooth (2.1+EDR)
- Encodage direct MP3 depuis un vinyle vers une clé USB
- Préamplificateur stéréo intégré
- 2 réglages de vitesse 33 tours et 45 tours
- Cellule à aimant mobile (MMC)
- Support du bras de lecture mécanique
- Courroie d'entraînement
- Semi-automatique
- Retour automatique
- Séparation de pistes
- Capot anti-poussière
- Connexion: Port USB

ES

- Bluetooth transmisión (2.1+EDR)
- Codificación MP3 directa desde vinilo a USB
- Preamplificador estéreo integrado
- 2 velocidades 33 RPM y 45 RPM
- Cápsula de Imán Móvil
- palanca de alzamiento/bajada del brazo mecánico
- Transmisión por correa
- Semiautomático
- Retorno automático
- Función track splitting (divisor de pistas)
- Cubierta extraíble
- Conexiones: Puerto USB

DATA :

- Power source : DC 12V
- Power consuming max : 5W
- Dim. unit: 420 x 362 x 118 mm (WxDxH)
- Dim. Gift box: 505 x 390 x 150 mm (WxDxH)
- Weight: 2.5 kg
- Master carton quantity: 2 pcs
- EAN-code: 8711902039822
- Custom code: 8519300000

Container quantity :

- 20'ft : 855pcs
- 40'ft : 1710pcs
- 40'HQ : 1950pcs

Subject to changes without prior notice

