

SteelSeries QcK Edge - XL

Produktbezeichnung	SteelSeries QcK Edge - XL																																
Beschreibung	The QcK Edge adds the extra durability of stitched edges to the legendary QcK micro-woven cloth found in the world's best-selling mousepad. More esports pros use QcK mousepads than any other gaming surface because of the reliable smooth surface, optimized for both optical and laser sensors.																																
Besonderheiten	Legendary Micro-Woven Cloth: With over 10 million sold, the SteelSeries QcK is the pinnacle of surface performance and innovation. Pinpoint Mouse Accuracy: Tested by the top mouse sensor manufacturer, the high thread count and smooth surface optimizes mouse tracking accuracy for both optical and laser sensors. Never-Fray Stitching: Stitching along the edges of the surface ensure it will never fray or peel. Never-Slip Base: The durable, non-slip rubber base is designed to eliminate unwanted movement and provide a solid platform for competitive gaming. Legendary Esports Status: For the past 15 years Esports stars have picked the SteelSeries QcK as their mouse pad of choice. Esports athletes have won more prize money using SteelSeries products than any other brand.																																
Verfügbar ab	Asien: - EMEA: - Amerika: -																																
Bestellnummer	63824																																
Lieferumfang	N/A																																
Technische Details	Abmessungen: 900mm x 2mm x 300mm / 35.433in x 0.078in x 11.811in																																
Systemanforderungen	N/A																																
Verpackung	<table><tr><td>Single:</td><td></td><td>Inner master:</td><td></td></tr><tr><td>Teile</td><td>1</td><td>Teile</td><td>6</td></tr><tr><td>Gewicht</td><td>460g / 1.016lbs</td><td>Gewicht</td><td>2910g / 6.431lbs</td></tr><tr><td>Höhe</td><td>310mm / 12.204in</td><td>Höhe</td><td>325mm / 12.79in</td></tr><tr><td>Breite</td><td>70mm / 2.755in</td><td>Breite</td><td>145mm / 5.708in</td></tr><tr><td>Tiefe</td><td>70mm / 2.755in</td><td>Tiefe</td><td>215mm / 8.464in</td></tr><tr><td>EAN</td><td>5707119036771</td><td>EAN</td><td>5707119036788</td></tr><tr><td>UPC</td><td>813682025625</td><td>UPC</td><td>-</td></tr></table>	Single:		Inner master:		Teile	1	Teile	6	Gewicht	460g / 1.016lbs	Gewicht	2910g / 6.431lbs	Höhe	310mm / 12.204in	Höhe	325mm / 12.79in	Breite	70mm / 2.755in	Breite	145mm / 5.708in	Tiefe	70mm / 2.755in	Tiefe	215mm / 8.464in	EAN	5707119036771	EAN	5707119036788	UPC	813682025625	UPC	-
Single:		Inner master:																															
Teile	1	Teile	6																														
Gewicht	460g / 1.016lbs	Gewicht	2910g / 6.431lbs																														
Höhe	310mm / 12.204in	Höhe	325mm / 12.79in																														
Breite	70mm / 2.755in	Breite	145mm / 5.708in																														
Tiefe	70mm / 2.755in	Tiefe	215mm / 8.464in																														
EAN	5707119036771	EAN	5707119036788																														
UPC	813682025625	UPC	-																														
Garantie	EU: 2 years manufacturer warranty US: 1 year manufacturer warranty Taiwan: 1 year manufacturer warranty <small>(Alle Produkte sind durch die örtlichen Garantiebestimmungen abgedeckt. Bitte erkundigen Sie sich bei Ihrem Händler, wenn Ihr Land nicht aufgelistet ist.)</small>																																
Zertifikate	RoHS, Grüne Punkt																																
Herkunftsland	Designed von SteelSeries in Dänemark, produziert in Taiwan.																																