

SAI Passive
SAI 4/6/8 MH-MHD BLZF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Cable gland: M25 for cables with an outer insulation diameter from 13 mm to 18 mm. The SAI distributor with M25 cable gland is suitable among others for the following cable types:

- 21 x 0.50 mm
- 18 x 0.75 mm bis 21 x 0.75 mm
- 14 x 100 mm bis 20 x 100 mm
- 8 x 1.50 mm bis 16 x 1.50 mm

General ordering data

| | |
|------------|--|
| Type | SAI 4/6/8 MH-MHD BLZF |
| Order No. | 1752083000 |
| Version | SAI Passive, Sensor-actuator passive distributor, Hood version with M25 outlet |
| GTIN (EAN) | 4032248269198 |
| Qty. | 640 pc(s). |

**SAI Passive
SAI 4/6/8 MH-MHD BLZF**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight 100 g

Temperatures

Operating temperature -

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Connection data

| | | | |
|----------------------|-------|----------------------|------------------------------|
| Conductor O.D., min. | 14 mm | Conductor O.D., max. | 18 mm |
| Cable glands | M 25 | Distributor outlet | Hood version with M25 outlet |

Electrical data

Max. current-carrying capacity per slot 4 A

Material data

| | | | |
|-----------------------|---------------------|------------------|------|
| Housing main material | Zinc diecast (hood) | Contact material | CuZn |
| Contact surface | Gold-plated | | |

Technical data cable

| | | | |
|----------------------|-------|----------------------|-------|
| Conductor O.D., min. | 14 mm | Conductor O.D., max. | 18 mm |
|----------------------|-------|----------------------|-------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 6.0 | EC002585 | eClass 6.2 | 27-06-91-90 |
| eClass 7.1 | 27-06-91-90 | eClass 8.1 | 27-06-91-90 |
| eClass 9.0 | 27-44-01-08 | eClass 9.1 | 27-44-01-08 |

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue [FL FIELDWIRING EN](#)