




Maßeinheit Millimeter, falls nicht anders angegeben
 Unless otherwise specified, dimensions are in millimeters

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)



Technische Daten
 siehe 06 6960 0001

Werkstoff / material		Nr. / no		Oberfläche / surface		Index / index	
		Masse / mass in g		Volumen / volume in cm ³		Toleranzen / tolerances	
		Maßstab / scale 1,5:1		Blattgröße / sheet size DIN A4			
Projektionsmethode 1 first angle projection		Datum / date		Name / name		Benennung / designation	
		Gezeichnet drawn 23.07.18		jbyckov		Kabelstecker cable plug connector 4+3+PE HEC	
Status state		Gepüft checked 23.07.18		fhoffmann			
50 - Freigegeben		Serie / series 696		Werkzeug / tool		Zeichnungs-Nr. / drawing no.	
01		20910		23.07.18		JB	
Rev rev		Nummer number		Datum date		Name name	
Ersatz f / replaces						99 6501 100 08 001	
						beb-intern / beb-internal	
						Blatt / sheet	
						von / of	