




Maßeinheit Millimeter, falls nicht anders angegeben  
 Unless otherwise specified, dimensions are in millimeters



Technische Daten  
 siehe 06 6960 0001

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)

Werkstoff / material		Nr. / no		Oberfläche / surface		Index / index	
		Masse / mass in g		Volumen / volume in cm <sup>3</sup>		Toleranzen / tolerances	
		Maßstab / scale		Blattgröße / sheet size		1,5:1 DIN A4	
Projektionsmethode 1 first angle projection		Datum / date		Name / name		Benennung / designation	
		Gezeichnet drawn		23.07.18		jbyckov	
		Geprüft checked		23.07.18		fhoffmann	
Status state		50 - Freigegeben		Serie / series		696	
Rev rev		01		20910		23.07.18	
Name name		JB		Werkzeug / tool		Zeichnungs-Nr. / drawing no.	
Ersatz f / replaces						99 6518 100 12 001	
						beb-intern / beb-internal Blatt / sheet von / of 001	