

BN 2134139

MIFARE RFID Tag

DE Kurzanleitung

Version: 2

Lieferumfang

- RFID-Tag (5x)

Beschreibung

Das Produkt ist ein RFID-Tag. Verwenden Sie es in Kombination mit einem kompatiblen Kartenleser/-schreiber.

Technische Daten

| | |
|-------------------------|-----------------|
| Typ | ISO14443 Type-A |
| Frequenz | 13,56 MHz |
| Identifizierungsbereich | 0 - 5 cm |
| Sendeleistung | 6 dBm |
| EEPROM Memory | 1 KB |
| Betriebstemperatur | -10 bis +75 °C |
| Abmessungen (ca.) | 3,5 x 2,8 cm |
| Gewicht (ca.) | 21 g |

Konformitätserklärung (DOC)

Hiermit erklärt Conrad Electronic SE, Klaus-Conrad-Straße 1, D-92240 Hirschau, dass dieses Produkt der Richtlinie 2014/53/EU entspricht.

Der vollständige Text der EU-Konformitätserklärung ist unter der folgenden Internetadresse verfügbar: www.conrad.com/downloads

Wählen Sie eine Sprache durch Anklicken eines Flaggensymbols aus und geben Sie die Bestellnummer des Produkts in das Suchfeld ein; anschließend können Sie die EU-Konformitätserklärung im PDF-Format herunterladen.

Entsorgung



Elektronische Geräte sind Wertstoffe und gehören nicht in den Hausmüll.

Entsorgen Sie das Produkt am Ende seiner Lebensdauer gemäß den geltenden gesetzlichen Bestimmungen.

Sie erfüllen damit die gesetzlichen Verpflichtungen und leisten Ihren Beitrag zum Umweltschutz.

Impressum

Dies ist eine Publikation der Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com)

Alle Rechte einschließlich Übersetzung vorbehalten. Reproduktionen jeder Art, z. B. Fotokopie, Mikroverfilmung, oder die Erfassung in elektronischen Datenverarbeitungsanlagen, bedürfen der schriftlichen Genehmigung des Herausgebers. Nachdruck, auch auszugsweise, verboten.

Die Publikation entspricht dem technischen Stand bei Drucklegung.
Copyright 2022 by Conrad Electronic SE.



BN 2134139

MIFARE RFID Tag

EN Quick Instructions

Version: 2

Delivery Content

- RFID Tag (5x)

Description

The product is an RFID tag. Use it in combination with a compatible card reader/writer.

Specifications

| | |
|-----------------------|-----------------|
| Type | ISO14443 Type-A |
| Frequency | 13.56 MHz |
| Identification range | 0 - 5 cm |
| Transmission power | 6 dBm |
| EEPROM Memory | 1 KB |
| Operating temperature | -10 to +75 °C |
| Dimensions (approx.) | 3.5 x 2.8 cm |
| Weight (approx.) | 21 g |

Declaration of Conformity (DOC)

Conrad Electronic SE, Klaus-Conrad-Straße 1, D-92240 Hirschau hereby declares that this product conforms to the 2014/53/EU directive.

Click on the following link to read the full text of the EU declaration of conformity: www.conrad.com/downloads

Select a language by clicking on a flag symbol and enter the product order number in the search box. You can then download the EU declaration of conformity in PDF format.

Disposal



Electronic devices are recyclable waste and must not be disposed of in the household waste.

At the end of its service life, dispose of the product in accordance with applicable regulatory guidelines.

You thus fulfill your statutory obligations and contribute to the protection of the environment.

Legal Notice

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited.

This publication represent the technical status at the time of printing. Copyright 2022 by Conrad Electronic SE.

