

DE Technische Daten Ladegerät

Input:	100-240V AC 50/60Hz 160mA
AC Primärstecker:	Euro Stecker
Standby-Verbrauch:	< 1W
Ladbare Akkutypen:	NiMH / NiCd
Anzahl Ladeschächte:	4x AAA/AAA oder 2x 9V
Ladestrom / Output:	4x 500mA (AAA/AA) 2x 13mA (9V)
Erhaltungsladung:	50m (AAA/AA)
dV	ja
Sicherheitstimer:	ja
Error-Erkennung:	Defekter Akku, nicht wiederaufladbare Batterie
Ausgangsschutz:	Mechan. Verpolschutz, Mechan. Kurzschlusschutz
LED:	4 Multifarb LED (rot/grün) pro Ladeschacht: - Laden: LED rot - Erhaltungsladung: LED grün (AAA/AA) - Akku aufgeladen: LED aus (9V) - Error-Erkennung: LED blinkt
Schutzart:	IP20
Gehäusematerial:	Kunststoff
Gehäusefarbe:	Schwarz
Betriebstemperatur:	0°C...25°C
Lagertemperatur:	-25°C...60°C
EMV Standards:	EN55014-1, EN55014-2, EN61000-3-2, EN61000-3-3
Sicherheitsstandards:	EN60335-2-29
Approbationen:	CE, GS
Verpackung:	Blisterkarte
Sprachen Verpackung:	DE, GB, FR, IT, ES, NL, CZ, PL, BG, RO, HU, HR, SK, TR, FI, GR
Sprachen Bedienungsanleitung:	DE
Lieferumfang:	Ladegerät, Bedienungsanleitung

DE Logistik Daten

Produkt-Abmessungen:	104x67x67mm
Produkt-Gewicht:	101g
Verpackungs-Abmessungen:	235x135x68mm
Verpackungs-Gewicht:	156g
EAN Verpackung:	4250040915338

GB Technical data charger

Input:	100-240V AC 50/60Hz 160mA
AC input socket:	Euro plug
Standby consumption:	< 1W
Rechargeable battery types:	NiMH / NiCd
Number of charging slots:	4x AAA/AAA or 2x 9V
Charge current / output:	4x 500mA (AAA/AA) 2x 13mA (9V)
Trickle charge current:	50m (AAA/AA)
dV	yes
Safety timer:	yes
Error detection:	Battery defect and alkaline detection
Output protection:	Mechanical wrong polarity and short circuit detection
LED:	4 multi-colour LED (red/green) per charging slot: - Charging: LED red - Trickle charge: LED green (AAA/AA) - Battery full: LED off (9V) - Error detection: LED flashes
Protection type:	IP20
Housing material:	Plastic
Housing colour:	Black
Operating temperature:	0°C...25°C
Storage temperature:	-25°C...60°C
EMC standards:	EN55014-1, EN55014-2, EN61000-3-2, EN61000-3-3
Safety standards:	EN60335-2-29
Approvals:	CE, GS
Package:	Blister card
Languages Package:	DE, GB, FR, IT, ES, NL, CZ, PL, BG, RO, HU, HR, SK, TR, FI, GR
Languages Manual:	DE
Shipment:	Charger, manual

GB Logistics data

Product dimensions:	104x67x67mm
Product weight:	101g
Package dimensions:	235x135x68mm
Package weight:	156g
EAN package:	4250040915338