



brennenstuhl®

SICHERHEITSINFORMATIONEN

SAFETY INFORMATION

DE	Sicherheitsinformationen	HU	Biztonsági információk	LT	Saugos informacija
EN	Safety information	RU	Информация о безопасности	LV	Drošības informācija
FR	Informations sur la sécurité	TR	Güvenlik bilgileri	HR	Sigurnosne informacije
NL	Veiligheidsinformatie	FI	Turvallisuustiedot	RO	Informații privind siguranța
IT	Informazioni sulla sicurezza	GR	Πληροφορίες για την ασφάλεια	BG	Информация за безопасност
SE	Säkerhetsinformation	PT	Informações de segurança	DK	Oplysninger om sikkerhed
ES	Información de seguridad	EE	Ohutusalane teave	NO	Sikkerhetsinformasjon
PL	Informacje dotyczące bezpieczeństwa	SK	Bezpečnostné informácie	UA	Інформація з техніки безпеки
CZ	Bezpečnostní informace	SI	Varnostne informacije	AR	معلومات السلامة

WWW.BRENNENSTUHL.COM

04/11/2024

SIZE: 90mm x 30mm



250V~ / 16A
MAX 3680W

CE IP44

0483979/0424

500-4019

4019 0424

Art.1 16145 0

Hugo Brennenstuhl GmbH &Co.KG

Seestr.1-3 D-72074 Tübingen

lectra technik ag,

Blegistr. 13, CH-6340 Baar

service@brennenstuhl.com

220mm

brennenstuhl®

10 m

Art. 1 16145 0

H05RR-F 3G1,5

Max. 3680W / 16A / 230V~



Io Riciclo
PLASTICA → PP 05
FASCETTA PER CAVI → 0 07
RACCOLTA DIFFERENZIATA
SEGUI LE REGOLE DEL TUO COMUNE
VALIDO SOLO IN ITALIA
VALID ONLY IN ITALY



Made in China
0457660/4222



Spritzwassergeschützt
Protected against splash water

**Für den
kurzfristigen
Gebrauch außen**

**For temporary
outside use**

0453466/5018

110mm