



Product Service

# CERTIFICATE

No. Z1A 011176 0929 Rev. 00

**Holder of Certificate:** **Hugo Brennenstuhl GmbH & Co KG**

**brennenstuhl®**

\_ smart technology.

Seestr. 1-3  
72074 Tübingen  
GERMANY

**Certification Mark:**



**Product:** **Multiple sockets**  
**Multiple socket outlets**

**Tested according to:** DIN VDE 0620-2-1:2016/A1:2017  
DIN VDE 0620-2-1:2021 Abschnitt 10.5  
AfPS GS 2019:01 PAK  
EK1 702-20 Rev. 1  
EK1 634-16

With this certificate, in its capacity as a notified GS body, TÜV SÜD Product Service GmbH issues the GS Mark to the named certificate holder for the declared product with the named model designation in accordance with section 20 ProdSG (German Product Safety Act). The product meets the safety and health requirements of section 20 (3) ProdSG. The manufacturer is reminded of their obligations in accordance with section 24 ProdSG. The certification marks shown above can be affixed on the product. It is not permitted to alter the certification marks in any way. In addition, the certificate holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the testing and certification regulations of TÜV SÜD Group have to be complied. For details see: [www.tuvsud.com/ps-cert](http://www.tuvsud.com/ps-cert)

**Test report no.:** 034-713216327-000

**Valid until:** 2026-01-01

**Date,** 2021-11-25

( Reinhold Hug )

# CERTIFICATE

No. Z1A 011176 0929 Rev. 00

**Model(s):** PRL 04 DE V2; PRL 06 DE V2; PLT P24 DE V2; PRL 08 DE V2;  
PRL 10 DE V2; POL 06 DE; PLT 05 DE V2; PLT 06 DE V2

## Parameters:

Rated voltage: 230V~  
 Rated current: 16A  
 Rated power: max. 3680W  
 Protection class: I  
 Degree of protection: IP20

Model/Series	Type	Sockets	Voltage	Length of power cord Type
Premium-Line	PRL 04 DE V2	4	230V~	1,8m H05VV-F 3G1,5mm <sup>2</sup> non-rewirable
	PRL 06 DE V2	6	230V~	3,0-5,0m H05VV-F 3G1,5mm <sup>2</sup> non-rewirable
	PLT P24 DE V2	6	230V~	3,0m H05VV-F 3G1,5mm <sup>2</sup> rewirable
	PRL 08 DE V2	8	230V~	3,0-5,0m H05VV-F 3G1,5mm <sup>2</sup> non-rewirable
	PRL 10 DE V2	10	230V~	3,0m H05VV-F 3G1,5mm <sup>2</sup> non-rewirable
Premium-Office-Line	POL 06 DE	6	230V~	3,0m H05VV-F 3G1,5mm <sup>2</sup> non-rewirable
Premium-Line 5x1	PLT 05 DE V2	5	230V~	3,0m H05VV-F 3G1,5mm <sup>2</sup> rewirable
Premium-Line 3x2	PLT 06 DE V2	6	230V~	3,0m H05VV-F 3G1,5mm <sup>2</sup> rewirable