



brennenstuhl®

SICHERHEITSINFORMATIONEN

SAFETY INFORMATION

DE	Sicherheitsinformationen	HU	Biztonsági információk	LT	Saugos informacija
EN	Safety information	RU	Информация о безопасности	LV	Drošības informācija
FR	Informations sur la sécurité	TR	Güvenlik bilgileri	HR	Sigurnosne informacije
NL	Veiligheidsinformatie	FI	Turvallisuustiedot	RO	Informații privind siguranța
IT	Informazioni sulla sicurezza	GR	Πληροφορίες για την ασφάλεια	BG	Информация за безопасност
SE	Säkerhetsinformation	PT	Informações de segurança	DK	Oplysninger om sikkerhed
ES	Información de seguridad	EE	Ohutusalane teave	NO	Sikkerhetsinformasjon
PL	Informacje dotyczące bezpieczeństwa	SK	Bezpečnostné informácie	UA	Інформація з техніки безпеки
CZ	Bezpečnostní informace	SI	Varnostne informacije	AR	معلومات السلامة

WWW.BRENNENSTUHL.COM

04/11/2024

100mm



250V~ / 16A
Max. 3680W



0483396/5023

516-3676K

Art. 1 16546 0

Hugo Brennenstuhl GmbH & Co. KG,
Seestr.1-3, D-72074 Tübingen

lectra technik ag, Blegistrasse 13, CH-6340 Baar
service@brennenstuhl.com

3676 0820

20mm

220mm

110mm

brennenstuhl®
10 m

Art. 1 16546 0

H05VV-F 3G1,5

Max. 3680W / 16A / 230V~



Io Riciclo
PLASTICA → PP 05
FASCETTA PER CAVI → O 07
RACCOLTA DIFFERENZIATA
SEGUI LE REGOLE DEL TUO COMUNE
VALIDO SOLO IN ITALIA
VALID ONLY IN ITALY



Made in China
0457666/1822

0453471/428

**Für den
Gebrauch innen**
Heim, Haus & Hobby

For indoor use
Home, house & hobby