



brennenstuhl®

SICHERHEITSINFORMATIONEN

SAFETY INFORMATION

DE	Sicherheitsinformationen	HU	Biztonsági információk	LT	Saugos informacija
EN	Safety information	RU	Информация о безопасности	LV	Drošības informācija
FR	Informations sur la sécurité	TR	Güvenlik bilgileri	HR	Sigurnosne informacije
NL	Veiligheidsinformatie	FI	Turvallisuustiedot	RO	Informații privind siguranța
IT	Informazioni sulla sicurezza	GR	Πληροφορίες για την ασφάλεια	BG	Информация за безопасност
SE	Säkerhetsinformation	PT	Informações de segurança	DK	Oplysninger om sikkerhed
ES	Información de seguridad	EE	Ohutusalane teave	NO	Sikkerhetsinformasjon
PL	Informacje dotyczące bezpieczeństwa	SK	Bezpečnostné informácie	UA	Інформація з техніки безпеки
CZ	Bezpečnostní informace	SI	Varnostne informacije	AR	معلومات السلامة

WWW.BRENNENSTUHL.COM


04/11/2024

尺寸:15.8X2CM

brennenstuhl®

Typ **MB 150 S**
Art.-Nr. **1440840**

Max.
150 kg



A
B
C
D
E
F

0177034/4723
Made in China

Hugo Brennenstuhl GmbH & Co. KG, Seestraße 1-3, D-72074 Tübingen
H. Brennenstuhl S.A.S., 4 rue de Bruxelles, F-67170 Bernolsheim

lectra technik ag, Blegistrasse 13, CH-6340 Baar
Brennenstuhl UK Ltd., No 1 Royal Exchange, London EC3V 3DG, UK

service@brennenstuhl.com




4 007123 112319



Stahl-Sägebock
Steel saw horse
Support de scie
Stalen zaagbok

MB 150 S

Pos.1	M 6 x 12		11 x
Pos.2	M 6		6 x
Pos.3	M 6		3 x
Pos.4	M 8		3 x
Pos.5	M 8		6 x
Pos.6	M 8 x 16		3 x
Pos.7	M 6 x 35		2 x
Pos.8	M 6		10 x

