

DE Technische Daten Kopflampe

LED Leuchtmittel:	3W LED + 5mm LED	
Funktionen Schalter 1:	1. Power-Modus 100%	
	2. Eco-Modus 50%	
	3. Stroboskop Licht	
	4 Aus	
	1. Rotes LED Licht	
	2. Rotes Stroboskop Licht	
	4. Aus	
Funktionen Schalter 2:	Sensor Modus: LED bei 100%	
LED Leistung:	100%	50%
Lichtstrom/Lumen (ca.):	140lm	67lm
Leuchtdauer (ca.):	3h	10h
Leuchtweite (ca.):	40m	25m
Farbtemperatur/CCT (ca.):	6000-8000K	
Farbwiedergabeindex:	CRI > 70	
Akkupack:	Li-Po 3,7V 1200mAh	
Risikogruppe (EN 62471):	2	
Ladezeit (ca.):	2,5h	
Eingangsbuchse:	Micro-USB Buchse	
Eingangsspannung:	5V DC	
Eingangsstrom:	500mA	
Ladeverfahren:	CCCV	
Gehäusematerial:	ABS + PC	
Farbe:	Schwarz	
Schutzklasse:	III	
Tiefentladeschutz:	Ja	
Ladezustandsanzeige:	Ladevorgang: Schalter leuchtet rot	
	Akku voll: Schalter leuchtet grün	
Ladetemperatur:	0°C...+35°C	
Betriebstemperatur:	-10°C...+40°C	
Lagertemperatur:	-20°C...+45°C	
Approbationen:	CE	
Verpackung:	Blister	
Sprachen Verpackung:	DE, GB, FR, IT, ES, PL	
Sprachen Bedienungsanleitung:	DE, GB, FR, IT, ES	
Lieferumfang:	Kopflampe, Kopfband, Micro-USB Kabel, Bedienungsanleitung	

DE Technische Daten Micro-USB Kabel

Eingangsstecker:	USB type A
Ausgangsstecker:	Micro USB type B
Länge:	50cm
Farbe:	Schwarz
Kabel-Typ:	Ladekabel

DE Logistik Daten

Produkt-Abmessungen:	60x45x35mm
Produkt-Gewicht:	70g (Lampe mit Akku) 20g (Akku)
Verpackungs-Abmessungen:	215x137x75mm
Verpackungs-Gewicht:	119g
EAN Verpackung:	4250040936425

DE Produktspezifische Hinweise

- Verwendungszweck: Stirnlampe. Nicht zur Verwendung in anderen Anwendungen bestimmt. Nicht für die Raumbeleuchtung im Haushalt geeignet
- Nur in geschlossenen Räumen aufladen
- 45° drehbares Gelenk

GB Technical data head light

LED illuminant:	3W LED + 5mm LED	
Functions switch 1:	1. Power-Mode 100%	
	2. Eco-Mode 50%	
	3. Strobe light	
	4. off	
	1. Red light	
	2. Red Strobe light	
	3. off	
Functions switch 2:	Sensor mode: LED at 100%	
LED power:	100%	50%
Luminous flux/Lumen (approx.):	140lm	67lm
Run time (approx.):	3h	10h
Beam distance (approx.):	40m	25m
Colour temperature/CCT (approx.):	6000-8000K	
Colour rendering index:	CRI > 70	
Rechargeable battery pack:	Li-Po 3,7V 1200mAh	
Risk group (EN 62471):	2	
Charging time (approx.):	2,5h	
Input socket:	Micro-USB socket	
Input voltage:	5V DC	
Input current:	500mA	
Charging method:	CCCV	
Housing material:	ABS + PC	
Colour:	Black	
Protection class:	III	
Deep discharge protection:	yes	
Charging status indicator:	Loading: Button lights up red	
	Battery full charged: Button lights up green	
Charging temperature:	0°C...+35°C	
Operating temperature:	-10°C...+40°C	
Storage temperature:	-20°C...+45°C	
Approvals:	CE	
Package:	Blister card	
Languages Package:	DE, GB, FR, IT, ES, PL	
Languages Manual:	DE, GB, FR, IT, ES	
Shipment:	Head light, head strap, Micro-USB cable, manual	

GB Technical data Micro-USB cable

Input plug:	USB type A
Output plug:	Micro USB type B
Length:	50cm
Colour:	Black
Cable type:	Charging cable

GB Logistics data

Product dimensions:	60x45x35mm
Product weight:	70g (lamp with battery pack) 20g (only battery pack)
Package dimensions:	215x137x75mm
Package weight:	119g
EAN package:	4250040936425

GB Product specific notes

- Intended purpose: head light. Not intended for use in other applications. Not suitable for household room illumination
- Only charge in closed rooms
- 45° turn able hinge