

M-22 USB Dynamisches Mikrofon | Schnellstart

Das M-22 USB ist ein dynamisches Mikrofon konzipiert für digitale Aufnahmen am Computer. Es ist ideal für Podcaster, Musiker, Journalisten und alle, die Audiofiles für Websites oder Multimediapräsentationen benötigen. Das Mikrofon ist kompatibel zu PC und Mac und wird dank seiner Plug-&-play-Funktionalität automatisch erkannt. Zum Lieferumfang gehört eine praktische Halterung.



Stellen Sie den Mikrofonständer auf und klemmen Sie das M-22 USB hinein. Schließen das Mikrofon an eine freie USB-Schnittstelle Ihres Computers an. Das Mikrofon wird vom Computer sofort als USB-Audiogerät unter dem Namen "USB-Microphone" erkannt. Mit den Standardwerkzeugen Ihres Betriebssystems können Sie es konfigurieren. Stellen Sie zum Einschalten den Schiebeschalter auf „ON“.

Hinweise

Wartungs- und Servicearbeiten sind ausschließlich dem autorisierten Fachhandel vorbehalten. Schäden, die durch manuelle Veränderungen an diesem Gerät verursacht werden, fallen nicht unter den Garantieanspruch. Wird das Mikrofon zweckentfremdet oder falsch angeschlossen, kann dies zu Schäden führen und der Garantieanspruch erlischt. Schützen Sie das Mikrofon vor Feuchtigkeit und Hitze. Die Umgebungstemperatur muss zwischen -5° C und +45° C liegen. Verwenden Sie zur Reinigung ein trockenes Tuch. Niemals Chemikalien oder Wasser.

Technische Daten

Typ:Dynamisch
Richtcharakteristik:Niere
Frequenzbereich: 100-12000 Hz
Impedanz:600 W
Empfindlichkeit:53 dB (±3 dB)
Anschluss:USB Typ A
Gewicht:200 g
Betriebssystem:Windows XP, Vista, 7, 8 und Mac OS X 10.3.9 oder höher

Änderungen vorbehalten.



M-22 USB Dynamic Microphone | Quick Start

The M-22 USB is a dynamic microphone designed for digital recordings at the computer. It is ideal for podcasters, musicians, journalists and anyone requiring recordings for websites or multimedia presentations. The microphone connects both PC and Mac and requires no setup thanks to its plug & play functionality. Delivery includes a practical stand.



Set up the microphone stand and insert the M-22 USB from above. Connect the microphone to an available USB port on your computer. It will be recognized by the computer as USB audio device under the name "USB-Microphone". You can control the microphone using the standard audio interface controls in the Mac and Windows operating system. Set the sliding switch to "ON" to switch on the microphone.

Notice

Maintenance and service operations are only to be carried out by authorized dealers. Damage, caused by manual modifications on this device is not subject to warranty. If the microphone is used for other purposes than originally intended or if it is not correctly connected, the product may suffer damages and the guarantee becomes void. Protect the microphone against humidity and heat. The ambient temperature must always be between -5°C and $+45^{\circ}\text{C}$. For cleaning the microphone only use a dry cloth. Never use chemicals or water.

Technical Specifications

Type:Dynamic
Directivity pattern:.....Cardioid
Frequency range:100-12000 Hz
Impedance:600 ohms
Sensitivity:53 dB (± 3 dB)
Connector:USB type A
Weight:.....200 g
Operating system:.....Windows XP, Vista, 7, 8 and Mac OS X 10.3.9 or better
Subject to change.