

KERN DS 150K1

KERN

Precision industrial scale with laboratory accuracy, ideal for the diverse possibilities of Industry 4.0 applications



Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	DS

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	150 kg
Readability [d]	0,001 kg
Reproducibility	0,001 kg
Linearity	± 0,003 kg
Resolution	150.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	150 kg (F1)
Possible calibration points	50 kg; 100 kg; 150 kg
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,005 kg
Construction type of the scale	Single-range balance

Units	kg
	g
	dwt
	tl (Tw)
	tl (HK)
	ozt
	tl (Singap, Malays)
	ct
	mo
	lb
	oz
	ffa

Maximum creep (15 minutes)	10 g
Maximum creep (30 minutes)	20 g
Default unit	kg

Display

Display type	LCD
Display backlight	✓
Display screen size	89×30 mm
Display digit height	21 mm
Languages of the user interface	English Symbol language

Construction

Dimension housing (W×D×H)	225×115×60 mm
Dimension display device (W×D×H)	225×115×60 mm
Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×125 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	metal, lacquered
Material display housing	plastic
Level indicator	✓
Levelling feet adjustable	✓
Stand height	450 mm
Wall mount	✓
Transport safety lock - bolt torque	0,1 Nm
Display device cable length	2,5 m

Functions

PreTare function	✓
Sum memory function	✓
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	None
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	150.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	1 g
Smallest piece weight when piece counting - normal conditions	10 g
Reference quantity	5, 10, 20, 50, n (any number of pieces)

KERN DS 150K1



Precision industrial scale with laboratory accuracy, ideal for the diverse possibilities of Industry 4.0 applications

Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
	30 sec
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	5

Interface

Interfaces	RS-232 (optional)
	Ethernet (optional)
	Bluetooth BLE (v4.0) (optional)
	USB-Device (optional)
	KUP
	WiFi (optional)
compatible with EasyTouch	✓

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	UK
	US
	CH
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	5,9V, 1A
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 13 mm
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	-10 °C
---------------------------	--------

Ambient temperature [Max]	40 °C
Humidity of environment [Max]	80 %

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkKS calibration	963-129
Article number for certificate of conformity	969-517

Packing & Shipping


Delivery time	1 d
Dimensions packaging (W×D×H)	595×505×240 mm
Shipping method	Parcel service
Net weight approx.	19 kg
Gross weight approx.	22 kg
Shipping weight	20,5 kg

Product information

GTIN/EAN number	4045761357037
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

