

tempmate.®-i1

➔ Single-Use Temperature Indicator for Cold Chain Temperature Monitoring



+ Break-Off Tab to Start the device

+ Small, light and flat design

+ GDP and EN12830 compliant



PHARMACEUTICAL
PRODUCTS



FOOD & PRODUCE



CHEMICAL
PRODUCTS

Single-Use Temperature Indicator for reliable low-cost cold chain monitoring.

tempmate.®-i1 indicators have 3 LED's onboard for indicating the alarm status easily, so no further software or hardware is required to check the condition of the goods.



© tempmate.com



Easy
handling



EN 12830
compliant



GDP
compliant




German
Quality



IP 67
protected



Temperature
-20°C to +50°C



Frontside

Curious about your cold chain?

tempmate.® continuously monitors all relevant data.

tempmate.®-i1 indicators are specially designed for temperature monitoring in pharmaceutical cold chain logistics. As pre-programmed device **tempmate.®-i1** can be instantly used to control your temperature sensitive consignment. By comparison to chemical indicators, the 3 LED's at the frontside of the electronic indicator gives you a fast and clear feedback of your goods condition.

Your Benefits at a Glance

- + Product-related temperature monitoring along the entire cold chain
- + Cost-effective and reliable
- + Smart design, intuitive operation
- + Waterproof and food compatible
- + No additional hardware or software required
- + Storage time 4 years
- + Intelligent LEDs for status monitoring

Technical Specifications

Recording options	Single-Use
Temperature range	-20 °C to 50 °C (-4 °F to 122 °F)
Temperature accuracy	±0.5 °C / 0.9 °F
Temperature resolution	0.1 °C / °F
Alarm indicator	red, green and blue LED
Shelf life / battery	4 years / 3.0 v lithium battery
Recording interval	1 minute
Runtime	up to 180 days
Startup mode	Break-Off-Tab
Start Delay / Alarm Delay	Programmable
Alarm Event	Single / Cumulative (Programmable)
Dimensions	50 mm × 33 mm × 5 mm (L × W × H)
Weight	approx. 10 g
Certifications	EN 12830, CE, RoHS
Calibration	3 Point Calibration
Packaging	Foodgrade PA/PE packaging
Protection Class	IP67 / NEMA 6

Part Number Selection

i1	Product
C	Temperature Unit Celsius or F = Fahrenheit
S	Alarm Type Single Event or C = Cumulative
1	Alarm Limits (1 = +2 to +8°C; 2 = +0 to +15°C; 3 = +15 to +25°C)
0	0 min Start Delay or 1 = 10 min
0	0 min Alarm Delay or 1 = 10 min

Available Configurations

i1CS100	+2 to +8°C no start delay, no alarm delay
i1CS110	+2 to +8°C start delay 10 mins, no alarm delay
i1CS200	0°C to +15°C no start delay, no alarm delay
i1CS300	+15°C to +25°C no start delay, no alarm delay
i1CS400	+1 to +40°C no start delay, no alarm delay

*Other configurations possible on request

